HM8040-3 Triple Power Supply Technical Data





Key facts

- 12x0-20V/0,5A 1x5V/1
- $\ensuremath{\text{\textbf{I}}}$ 3-digit switchable displays for current and voltage
- Display resolution 0.1 V/1 mA
- Adjustable current limiting
- Linear inline regulator
- I Low residual ripple and low noise
- Pushbutton for activating/deactivating all outputs
- Electronic fuse
- Mainframe HM8001-2 required for operation



Test & Measurement

Technical Data

HM8040-3 All data valid at 23 °C after 30 minutes warm-up. Outputs				
			2 x 0-20V and 5V	Single pushbutton control of all outputs linear regulators with overheatingprotection. Floating outputs forparallel/serial operation, current limit andelectronic fuse
			20 V Output	
Setting range:	2 x 0 – 20V, continuously variable			
Residual ripple:	≤ 1 mVrms			
Output current:	max. 0.5A			
Current limit /electronic fuse:	0 – 0.5A continuously variable			
Dynamic behaviour:	Load change 10% - 90% of full load			
Recovery time:	200 μs			
Dyn. transient deviation:	typ. 2 mV			
Dyn. output impedance:	$3,75~\text{m}\Omega$			
Load change at 50% basic load	d and ±10% of full load			
Recovery time:	150 μs			
Dyn. transient deviation:	400 μV			
Dyn. output impedance:	4 mΩ			
5V Output				
Range:	5V ±0.5V screw-driver adjustment			
Ripple and noise:	≤ 1 mVrms			
Output current:	max. 1 A continuous, short-circuit-proof			
Combined displays of 20V	outputs			
7-segment LED:	2 x 3-digit displays, each switchable forvoltage and current (V, mA)			
Resolution:	0.1 V / 1 mA			
Display accuracy:	±1 digit voltage ±4 digit current			
LED:	current limit indication			

Maximum limits		
Reverse voltage:	25 V, each output	
Reverse current:	500 mA, each output	
Voltage to ground:	100 V, each terminal	
Temperature control:	If the inside temperature exceeds 7580°C, the instrument will be turned off.	
Miscellaneous		
Safety class:	Safety class I (EN61010-1)	
Power supply (from mainframe):	1x 8V/1A 2x24V/530 mA 1x 5V/400 mA 1x18VAC/100 mA Σ = 40 W	
Current output of 2 HM8040-3 with HM8001-2:	sum of all channels ≤2 A	
Operating temperature:	+5 °C to +40 °C	
Storage temperature:	-20 °C to +70 °C	
Max. relative humidity:	5% 80% (without condensation)	
Dimensions (W x H x D):	135 x 68 x 228 mm	
Weight:	approx. 1.07 kg	

Included in delivery:

HM8040-3 Triple Power Supply, Manual

Optional accessories:

HZ10S/-R/-B Silicon-insulated cable