

Capacitor, Tantalum, 150 uF, 7343, +/-20% Tol, 16 VDC (105C), Failure Rate=A (Non-ER)



General Information	
Supplier:	KEMET
Application:	Military COTS/Upscreened/Low ESR (Non-ER)
Sub Application:	(NonCombustibleCathode)
Part Type Description:	SMD, Polymer, Molded, COTS, Up Screening
Construction:	Standard Chip-Polymer
Body Type:	SMD Chip
Termination:	Solder Coated
Footprint:	7343
Weight:	588.16 mg
RoHS:	No

Dimensions (mm)		
Symbol	Dimension	Tolerance
L	7.3	+/-0.3
W	4.3	+/-0.3
H	4	+/-0.3
F	2.4	+/-0.1
S	1.3	+/-0.3
B	0.5	+/-0.15
X	0.1	+/-0.1
P	1.7	REF
R	1	REF
T	0.13	REF
A	3.8	MIN
G	3.5	REF
E	3.5	REF

Specifications	
Capacitance:	150 uF
Tolerance:	+/-20%
Voltage:	16 VDC (105C)
Temperature Range:	-55/+105C
Testing:	10 Cycles Surge Current Testing At -55C And +85C
Current/Ripple Current:	3143 mAmps (100kHz 45C)
Resistance/ESR:	25 mOhms (100kHz)
Failure Rate:	A (Non-ER)
Leakage Current:	240 uA
Dissipation Factor:	10%

Notes:
 -In Polarity Stripe, At KEMET's Option, Type May Be Indicated:
 No Symbol = Standard (Or Low Leakage) MnO2 Tantalum Chip,
 O = Low ESR T494, R = Low ESR T495, F = Fused T496, HT = 150C Rated T498 (or B45196P, B45198P), H = 175C Rated T499, H2 = 200C Rated T5

Packaging Specifications	
Package Kind:	T&R
Package Size:	7 in/180 mm
Package Quantity:	500

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.