


**KEMET Part Number: C323C103MCR5TA**  
(C323C103MCR5TABULK)

Capacitor, ceramic, 0.01 uF, +/-20% Tol, 500 V, X7R, Lead Spacing=0.2"



Dimensions (mm)		
Symbol	Dimension	Tolerance
L	5.08	MAX
H	7.62	MAX
T	3.81	MAX
S	5.08	NOM
LL	7	MIN
F	0.51	NOM

Packaging Specifications	
Package Kind:	Bulk
Package Type:	Bag
Package Quantity:	500

General Information	
Supplier:	KEMET
Application:	General Purpose
Temperature Coefficient:	X7R
Body Type:	Radial Conformal
Lead Type:	Formed
Termination Type:	Tin (Sn)
RoHS:	Yes

Specifications	
Capacitance:	0.01 uF
Voltage:	500 V
Tolerance:	+/-20%
Temperature Range:	-55/+125C
Failure Rate:	N/A
Dissipation Factor:	2.5%
Insulation Resistance:	100 GOhm
Dielectric Strength:	750 V