

Capacitor, Tantalum, SMD, MnO2, Molded, Fused, 10 uF, 6032, +/-10% Tol, 25 VDC (85C)



General Information	
Supplier:	KEMET
Application:	General Purpose
Sub Application:	(IntegralFuse)
Part Type Description:	SMD, MnO2, Molded, Fused
Construction:	Standard Chip/Fused-MnO2
Body Type:	SMD Chip
Footprint:	6032
Weight:	224.48 mg
RoHS:	Yes

Dimensions (mm)		
Symbol	Dimension	Tolerance
L	6	+/-0.3
W	3.2	+/-0.3
H	2.5	+/-0.3
F	2.2	+/-0.1
S	1.3	+/-0.3
B	0.5	+/-0.15
X	0.1	+/-0.1
P	0.9	REF
R	1	REF
T	0.13	REF
A	2.5	MIN
G	2.8	REF
E	2.4	REF

Specifications	
Capacitance:	10 uF
Tolerance:	+/-10%
Voltage:	25 VDC (85C)
Voltage:	16.75 VDC (125C)
Temperature Range:	-55/+125C
Current/Ripple Current:	428 mAmps (25C)
Current/Ripple Current:	385.2 mAmps (85C)
Current/Ripple Current:	171.2 mAmps (125C)
Resistance/ESR:	600 mOhms (100kHz)
Failure Rate:	N/A
Leakage Current:	2.5 uA
Dissipation Factor:	6%

Packaging Specifications	
Package Kind:	T&R
Package Size:	7 in/180 mm
Package Quantity:	500

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.