



Datasheet for part number KPT01F18-32P

| |
|--|
| Our Catalog Part Number: KPT01F1832P |
| Brand: Cannon Product Category: Circular Product Line: MIL-DTL 26482 Series I & Mil Battery Series: KPT / SE |

| | |
|--|--|
| Product Datasheet | |
| Shell Style | Cable connecting plug |
| Endbell Style | Grommet seal with strain relief |
| Gender | Pin |
| Shell Size | 18 |
| Contact Arrangement | 18-32 |
| Number of contacts | 32 contacts size 20 |
| Contact Type | Solder Cup |
| Contact Plating | Copper alloy, gold plated |
| Shell Material | Aluminium alloy |
| Shell Plating | Olive drab chromate over cadmium plating |
| Insulator and Gromet Material | Polychloroprene |
| Contact Material | Copper alloy, gold plated |
| Water Tightness | Acc. To VG95319 Part 2, Test No. 5.9.2 |
| Operating Temperature | -55°/+125°C (-67/257°F) |
| Mating Cycles | 500 min |
| Vibration | 200 m/s ² at 10 to 2000 Hz |
| Contact Rating AWG20 | 7,5 A |
| Insulator Resistance | ≈5000 MOhm |
| Test Voltage | 1500 Vrms |
| Operating Voltage | In case of voltages greater than 50V the connector must be used in accordance with DIN VDE part 410, IEC 60364-4-41. |
| Safety Provisions | IP67 acc. to DIN 40 050 (0,2 bar pressure over 48 hrs) |
| General Info | <i>All tests in accordance with VG95319 and/or if applicable with VG95210</i> |
| Harnessing Info: Contact Cross-Section | See assembly instruction |
| Harnessing Info: Insulator Diameter | See assembly instruction |