



Datasheet for part number CA3108F20-19PXB15

| |
|--|
| Our Catalog Part Number: CA3108F20-19PXB-15 |
| Brand: Cannon Product Category: Circular Product Line: CA Bayonet Series: CA BAYONET |

| | |
|---|---|
| Product Datasheet | |
| Bayonet | Connector with bayonet coupling |
| Shell Style | Plug, 90° |
| Endbell Style | Shielded connector with endbell for shielded braids and heat shrinkable boots |
| Gender | Pin |
| Shell Size | 20 |
| Contact Arrangement | 20-19 |
| Number of contacts | 3 contacts size 8 |
| Contact Type | AWG Crimp |
| Contact Plating | Hard silver |
| Shielding | yes |
| Insulator Rotation | 180° |
| Contact Rating at +20 °C (68 °F) (Size 60/100/8) | 74 A |
| Contact Resistance (Size 60/100/8) | 1 mΩ |
| Wire Cross Section | AWG 8 |
| Operating Voltage | In case of voltages greater than 50V the connector must be used in accordance with DIN VDE part 410, IEC 60364-4-41. |
| Insulator Resistance | Acc. To VG95319, part 2, test no. 5.12 and VG95210, part 32, test conditions B, standard insulator material > 1000 MΩ |
| Test Voltage | 2000 Vrms |
| Air and Creepage Paths (Min) | 1,1 mm |
| Ambient Temperature | Standard insulator material -55°/+125°C (-67/257°F) |
| Safety Provisions | IP67 and IP68 (1 bar pressure after 12 hrs) acc. to DIN 40 050 |
| Salt Spray Resistance | 500 hours salt spray resistant |
| Mating Cycles | 500 min |
| Sep. Force per Contact (Size 60/100/8) | 3,0 N |
| Gage | For infos on Gage please see catalog VG95234, part 1 |
| Coupling Torque | Closing: 9 Nm max / Opening: 0,7 Nm min |
| Contact Retention (Size 60/100/8) | 80 N |
| Shell Material | Aluminium alloy |
| Shell Plating | Olive drab chromate over cadmium plating (conductive) |
| Insulator and Grommet Material | CR-Elastomere |
| Contact Material | Copper alloy |
| Harnessing Info: Contact Cross-Section | See assembly instruction |
| Harnessing Info: Insulator Diameter | See assembly instruction |
| Wire Stripping (Size 60/100/8) | 11,8 mm |
| General Info | <i>All tests in accordance with VG95319 and/or if applicable with VG95210</i> |