


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	RELEASED FOR PRODUCTION	5/2/01	TJC
B	REVISED DRAWING FORMAT, UP-DATED SPECIFICATIONS NOTE (ECN# 1261)	2/4/03	T CLARK
.	.	.	.
.	.	.	.



MODEL NUMBER	LENGTH (FEET)
CSM25MF-2.5	2.5
CSM25MF-5	5.0
CSM25MF-10	10.0
CSM25MF-15	15.0
CSM25MF-25	25.0
CSM25MF-50	50.0

SPECIFICATIONS:

WIRING: STRAIGHT THROUGH, PIN TO PIN, ALL PINS.

SHIELD: DRAIN WIRE TIED TO CONNECTOR SHELLS

ELECTRICAL:

VOLTAGE RATING: 300V
 DIELECTRIC STRENGTH: 1500V

MATERIALS:

CONNECTORS: INSULATORS: THERMOPLASTIC, UL 94V-0, BLUE
 CONTACTS: COPPER ALLOY, GOLD OVER NICKEL
 SHELLS: STEEL, TIN PLATED
 HOOD MOLDINGS: PVC, GRAY
 INTERNAL SHIELD: METAL FOIL OVER PRE-MOLD (360°)
 CABLE: U.L. STYLE 2464 25 CONDUCTORS 26 AWG STRANDED TINNED COPPER
 OVERALL SHIELD: ALUMINIZED POLYESTER WITH DRAIN WIRE (100%)
 JACKET: PVC, GRAY
 HARDWARE: 4-40 THREAD, STEEL OR BRASS, NICKEL PLATED

ENVIRONMENTAL:

TEMPERATURE RANGE: -20°C TO 80°C

(REFERENCE L-COM CABLE SPECIFICATION CSM-CS1)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES TOLERANCES ARE:
 X ±.1
 .XX ±.05
 .XXX ±.005
 CABLE LENGTH TOLERANCE
 <300" ±5% >300" ±2%

APPROVALS	DATE
DRAWN BY TJC	5/21/01
CHECKED BY DFP	4/30/01
APPROVED BY CM	5/2/01

CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY

L-com
 CONNECTIVITY PRODUCTS

45 BEECHWOOD DRIVE
 NORTH ANDOVER, MA
 01845

PRODUCT DESCRIPTION
ECONOMY DATA CABLE ASSEMBLY

DRAWING TITLE
OUTLINE DRAWING

SIZE A	FSCM NO. 43321	DWG. NO. CSM25MF-2.5-OD1	REV. B
SCALE: 1:1	CAD FILE: CSM25MF-2.5-OD1.SLDDRW	SHEET 1 OF 1	