



SIMCO IONTM
An ITW Company

Top GunTM Ionizing Air Gun

TOP GUN

4007059 Top Gun Sidekick (For HANDS-FREE Operation)

Simco-Ion's Top Gun Ionizing Air Gun is a high-performance ionizing air gun designed for a wide variety of electronic manufacturing, medical and assembly applications. Balanced to $0\pm 15V$, the Top Gun features high blow-off force and low air consumption providing high efficiency cleaning and maximum static charge decay. A filter at the exit of the gun ensures that the air is clean.

The gun body is lightweight but durable. It features a light-touch trigger, making it comfortable even for extended use. All functionality is built into the gun, including

a flow control valve, a balance adjustment for calibration, and a two level LED which indicates both power and ionization. Both the gun and cable are static dissipative. A hanger is provided for easy mounting.



Features

- Lightweight, Ergonomic Design
- Flow Control Valve for Adjustable Airflow
- Electrically balanced ion output
- Integrated, Replaceable Filter-Nozzle
- Ionization Indicator Light

Benefits

- Maximum user comfort prevents operator fatigue and increases productivity
- Airflow use that meets the specific application requirements
- Protects ESD sensitive components and assemblies
- Insures air contacting the target area is clean
- Eliminates the guesswork of ionization at target area

Specifications

Top Gun 3	
Input Voltage	120 VAC, 60 Hz, 0.2A; 230 VAC, 50 Hz, 0.1A
Discharge	1.3 sec @ 6" (15.2 cm), 30 psi ($\pm 1000-100V$); 0.5 sec @ 2" (5 cm), 60 psi ($\pm 1000-100V$) ¹
Balance	$\pm 15V$
Flow	2.4 scfm @ 30 psi (68/min, 2 bar); 4.6 scfm @ 60 psi (130/min, 4 bar); 7.4 scfm @ 100 psi (210/min, 7 bar)
Blow-off Force	180g @ 100 psi, 2" diameter target 3" from the gun
Air Pressure	Pressure relief in nozzle complies with OSHA requirements
Audible Noise	76 dbA @ 30 psi input (2 bar); 89 dbA @ 60 psi input (4 bar); 97 dbA @ 100 psi input (7 bar); measured 24" (600 mm) from nozzle
Operating Env.	Temperature: 32-104°F (0-40°C); humidity: 30-60% RH (non-condensing)
Ozone	0.001 ppm measured 18" (450 mm) from gun, operation @ 15 psi (1 bar)
Filter	0.01 micron rating; replacement filters available
Gas Input	100 psi max; Clean Dry Air (CDA) or Nitrogen
Gas Connection	1/4" NPT (female)
Air Hose	Static dissipative polyurethane, 7' or 14' standard, 5' or 14' with optical sensor (integral to gun and control module)
Enclosure	Gun: Static dissipative polycarbonate/ABS blend; cable: static dissipative polyurethane
Dimensions	Gun: 6.5 oz (185g); air hose: 1.25 ounces/ft (115g/m)
Warranty	2 year limited warranty
Certification	 230V, 50 Hz  120V, 60 Hz (except versions w/optical sensor)
Control Module	
Power	120 VAC, 50/60 Hz, .10A; 230 VAC, 50/60 Hz, .05A
Power Inlet	IEC 320
Pressure	Maximum 100 psi Clean Dry Air Or Nitrogen (7 bar) 1/4" NPT connector, female
Dimensions	5.20W x 6.45H x 3.35D in. (132 x 164 x 85 mm)
Enclosure	Powder-coated steel
Weight	6 lbs (2.7 kg)

Top Gun with Optional Sidekick



The Top Gun with Sidekick offers hands-free operation and flexible positioning during assembly and manufacturing processes. A foot pedal controls both ionization and airflow, which reduces compressed air costs and extends the life of the ionizer. The flexible gun mount allows the operator to focus the ionized airflow where it is needed. The stand includes a steel bracket for easy bench-top mounting.

- Fully adjustable 18 inch neck focuses the ionized airflow
- Tabletop bracket provides easy mounting
- Foot pedal permits hands-free operation

Top Gun with Optical Sensor



For automated assembly, all versions of the Top Gun are available with an optional Optical Sensor, which automatically activates the gun when an object is in range. The Optical Sensor has an “adjustable range” from 1-30 inches.

Applications

- Medical device manufacturing and packaging
- Precision parts assembly
- Particulate removal in optics
- Cleaning glass or molded parts prior to finishing
- Cleaning thermo-formed trays



An ITW Company

DS-TopGun 5200870_V2 - 12/13
© 2013 Simco-Ion
All rights reserved.

Simco-Ion

Technology Group
1750 North Loop Rd., Ste 100
Alameda, CA 94502

Tel: 800.367.2452 (in USA)

Tel: 510.217.0600

info@simco-ion.com

www.simco-ion.com