



3-Position Key Operated Selector Switches, Non-Illuminated




Key Operated Selector Switch  
Cat. No. 800FP-KM31R



Key Operated Selector Switch  
Cat. No. 800FM-KM31R

Switching Angle



Target Table and Operator Position				
Contact Type	Position on Mounting Latch			
		N.O.	Left	X
N.O.	Right	O	O	X
N.O.	Center	X	O	X
N.C.	Left	O	X	X
N.C.	Right	X	X	O
N.C.	Center	O	X	O

Note: X = Closed/O = Open

Key Removal Position	Operator Position			Key Selector Switch Operators		Pkg. Quantity
				Plastic Cat. No.	Metal Cat. No.	
Left				800FP-KM31	800FM-KM31	1
All				800FP-KM33	800FM-KM33	
Center				800FP-KM34	800FM-KM34	
Center				800FP-KB34	800FM-KB34	

800F          -                        

a                      b                      c                      d                      e

*a*

Operator Construction	
Code	Description
P	Round plastic operator (IP66, Type 4/13)
M	Round metal operator (IP66, Type 4/13)

*c*

Key Removal Position*	
Code	Type
1	Left
3	All
4	Center
5	Left/center

*d*

See page 28 for optional key codes: †‡§

*b*

Operator Type	
Code	Description
KM3	Maintained
KR3	Spring return from right
KL3	Spring return from left
KB3	Spring return from both

*e*

Packaging	
Code	Description
Blank	1 per package
BP	10 per package

\* Key removal in maintained positions only.  
 † Keyed operators are IP66, Type 4/13.  
 ‡ Not intended for high security applications. Interoperability is possible with certain key/cylinder lock combinations. Consult your local Allen-Bradley distributor for interoperability information.  
 § For Ronis replacement keys, see Accessories, page 53.