






- *NEW* 17.5mm DIN rail housing
- **Supply Initiated Delay On Operate timing function**
- 7 Selectable time ranges (0.1 seconds 100 hours)
- Fine adjustment of selected time range
- Multi-voltage input (12 - 230V AC/DC)
- 1 x SPDT relay output 8A
- Green LED indication for supply / timing status
- **Red LED indication for relay status**
- Conforms to IEC 61812

FUNCTION DIAGRAM



LED operation.



INSTALLATION AND SETTING

- BEFORE INSTALLATION, ISOLATE THE SUPPLY.

Connect the unit as required.

Installation work must be carried out by qualified personnel.

Setting the unit.

- Set the "Range" 4 to the required position (depending on whether seconds, minutes or hours are required).
- Set the "Set %" adjustment 3 as required. The "Set %" is a % of the selected range; so for example, a 30% setting on the 1-10 hour range will give 3 hours.

- Apply power across terminals "A1" and "A2" and the green LED 1 will start flashing indicating timing in progress.
- The relay will remain de-energised (contacts 15 / 16 closed and 15 / 18 open) and red LED 2 extinguished.
- After the delay period "t" has elapsed, the relay will energise (contacts 15/16 open and 15/18closed) and the red LED will illuminate
- The green LED will remain permanently lit.
- The whole timing process is repeated by removing and re-applying power.


Note:

 1 In accordance with IEC 61812. the areen LED is permitted to extinauish durina a voltage dip or momentary interruption of the power supply providing the state of the output relay does not change. The dip / interruption duration and levels are defined in the product standard

Supply voltage U (A1, A2): 12 - 230V AC/DC 48 - 63Hz (AC supplies) Frequency range Supply variation +/ - 15% III (IFC 60664) Overvoltage category: Rated impulse withstand voltage 4kV (1.2/50μS) IEC 60664 Power consumption (max.): 12V 24V 110V 230V 0.4VA AC. 0.3VA 1.3VA 3.4VA 0.26W 0.24W 0.95W Timing function: Delay On Operate (Supply Initiated) Timing ranges (7): Seconds: Minutes Hours: 0.1 - 1 0.1 - 1 0.1 - 1 1 - 10 1 - 101 - 1010 - 100 Reset time: 100mS ± 1% of maximum full scale Accuracy: Adjustment accuracy < 5% of maximum full scale Repeat accuracy: $\pm\,0.5\%$ at constant conditions (IEC 61812) Drift with temperature ±0.05% / °C ± 0.2% / V Drift with voltage Green LED Power on indication / Timing¹ Relay status Red LED Ambient temp: -20 to +60°C Relative humidity +95% Output (15, 16, 18) SPDT rela Output rating 250V 8A (2000VA) AC1 AC15 250V 5A (no), 3A (nc) DC1 25V 8A (200W) Electrical life: ≥ 150,000 ops at rated load 2kV AC (rms) IEC 60947-1 Dielectric voltage: Rated impulse withstand voltage 4kV (1.2/50μS) IEC 60664 Housing: Orange flame retardant UL94 ≈ 60g Weight: On to 35mm symmetric DIN rail to BS EN 60715 Mounting option: or direct surface mounting via 2 x M3.5 or 4BA screws using the black clips provided on the rear of the unit.

TECHNICAL SPECIFICATION


CONNECTION DIAGRAM



SETTING DETAILS


1. Power supply status / Timing (Green) LED 2. Relay output status (Red) LED 3. "Set %" adjustment 4. Time delay "Range"

selector



Terminal conductor size

Approvals:



≤ 2 x 2.5mm² solid or stranded Conforms to IEC 61812.

80MHz - 2 7GHz) Emissions: EN 61000-6-4

CE, C-tick Cand RoHS Compliant.

EMC: Immunity: EN 61000-6-2 (EN 61000-4-3 10V/m

