

## Sample set - SAMPLE PTSM 0,5/ 8-HTB...SMDWH - 1847193

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Header, Nominal current: 6 A, Rated voltage (III/2): 160 V, Pitch: 2.5 mm, Color: white, Contact surface: Tin, Mounting: SMD soldering


The illustration shows a 3-position version

### Why buy this product

- Compatible with PTSM.../PTPM... plugs
- High current carrying capacity of 6 A
- Supplied in tape-on-reel packing according to IEC 60286-3 for automated mounting
- Rugged solder anchor for secure, mechanical fixing to the surface
- Specifically designed for use in dedicated SMT processes



### Key Commercial Data

Packing unit	5 pc
Minimum order quantity	5 pc
GTIN	 4 055626 003160
Weight per Piece (excluding packing)	2.22 g
Custom tariff number	85369010
Country of origin	Germany

### Technical data

#### Dimensions

Pitch	2.50 mm
Dimension a	17.5 mm

#### General

Insulating material group	I
Rated surge voltage (III/3)	2.5 kV
Rated surge voltage (III/2)	2.5 kV

# Sample set - SAMPLE PTSM 0,5/ 8-HTB...SMDWH - 1847193

## Technical data

### General

Rated surge voltage (II/2)	2.5 kV
Rated voltage (III/3)	125 V
Rated voltage (III/2)	160 V
Rated voltage (II/2)	250 V
Nominal current $I_N$	6 A
Maximum load current	6 A
Insulating material	HT PA
Flammability rating according to UL 94	V0
Color	white

### Standards and Regulations

Flammability rating according to UL 94	V0
--	----


## Classifications

### eCl@ss

eCl@ss 5.1	27141190
eCl@ss 6.0	27261101
eCl@ss 8.0	27440402
eCl@ss 9.0	27440402

## Drawings

Drilling diagram



Dimensional drawing

