



Classic LEDspotMV

CLA LEDspotMV D 4.4-35W GU10 827 36D

Featuring a classic heritage design, Classic LEDspotMV delivers warm halogen-like light while saving around 90% on energy costs. It is compatible with most existing fixtures with a GU10 holder and is designed as a retrofit replacement for halogen or incandescent spots. LED lamps deliver significant energy savings and minimise maintenance costs.

Product data


General Information		Wattage equivalent	
Cap base	GU10 [GU10]		35 W
Bulb shape	PAR16 [PAR 2 inch]	Starting time (nom.)	0.5 s
Nominal lifetime (nom.)	15000 h	Warm-up time to 60% light (nom.)	0.5 s
Switching cycle	50000X	Power factor (nom.)	0.70
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Beam Angle (Nom)	36 °	T-Case maximum (nom.)	80 °C
Luminous intensity (nom.)	500 cd		
Colour designation	Warm white (WW)	Controls and Dimming	
Rated beam angle	36 °	Dimmable	Yes
Correlated colour temperature (nom.)	2700 K		
Luminous efficacy (rated) (nom.)	57 lm/W	Approval and Application	
Colour consistency	<6	Energy-saving product	Yes
Color rendering index (nom.)	80	Suitable for accent lighting	Yes
LLMF at end of nominal lifetime (nom.)	70 %	Energy efficiency label (EEL)	A+
Luminous Flux In 90° Cone (Rated)	250 lm	Energy Consumption kWh/1000 h	5 kWh
Operating and Electrical		Product Data	
Input frequency	50-60 Hz	Full product code	871869656558200
Power (Rated) (Nom)	4.4 W	Order product name	CLA LEDspotMV D 4.4-35W GU10 827 36D
Lamp current (nom.)	25 mA	EAN/UPC – product	8718696565582

Classic LEDspotMV

Order code	56558200
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001218602

Net weight (piece)	0.036 kg
--------------------	----------

Dimensional drawing



GU10 230V 5W-50W 385lm 36D 4000K GU10 ND

Product	D	C
CLA LEDspotMV D 4.4-35W GU10 827 36D	50 mm	53 mm

Photometric data

Accent Lighting - Spots

