

Classic filament LED Lamps

CLA LEDBulb D 7.5-48W A60 E27 820 GOLD

Featuring a classic heritage design, Classic filament LED Lamps combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap base	E27 [E27]
Bulb shape	A60 [A 60mm]
Nominal lifetime (nom.)	15000 h
Switching cycle	20000X
Technical type	7.5-48W

Light Technical	
Luminous flux (nom.)	600 lm
Luminous flux (rated) (nom.)	600 lm
Colour designation	Flame
Correlated colour temperature (nom.)	2000 K
Luminous efficacy (rated) (nom.)	80.00 lm/W
Colour consistency	<6
Color rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical	
Input frequency	50-60 Hz

Power (Rated) (Nom)	7.5 W
Lamp current (nom.)	42 mA
Wattage equivalent	48 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.7
Voltage (Nom)	220-240 V

Controls and Dimming	
Dimmable	Yes

Approval and Application	
Energy-saving product	Yes
Suitable for accent lighting	No
Energy efficiency label (EEL)	A+
Energy Consumption kWh/1000 h	8 kWh


Product Data	
Full product code	871869657567300

Classic filament LED Lamps

Order product name	CLA LEDBulb D 7.5-48W A60 E27 820 GOLD
EAN/UPC – product	8718696575673
Order code	57567300
Numerator – quantity per pack	1
Numerator – packs per outer box	10

Material no. (12NC)	929001228102
Net weight (piece)	0.030 kg

Dimensional drawing



filament 7W-60W 620lm NAD 2200K E27D

Product	D	C
CLA LEDBulb D 7.5-48W A60 E27 820 GOLD	60 mm	112 mm

Photometric data

General Uniform Lighting

