




Features:

- Universal Full Range AC Input
- Small & Compact UK Plug design
- Level 6 Efficiency
- Cost Effective & Highly Reliable
- 1 Year Warranty
- Switch-mode power supply



Characteristics	
Part Number	T6117ST
AC Input Voltage Range	90-264 VAC
AC Input Frequency Range	47 - 63 Hz
AC Input Current	0.5A Max
AC Inrush Current	AT FULL LOAD, 25 DEGREE C, COLD START - No damage shall be occurred and the input fuse shall not be blown.
Input Plug Type	Wall-mount type, UK-pin, 3 Conductors, < Live, Neutral >
Power Consumption	115/230VAC INPUT , power consumption less than 0.1W
DC Ouput Voltage	12VDC
Minimum Load Current	0 A
Nominal Load Current	1 A
Nominal Output Power	12 W
Output Regulation	+ / - 5%
Ripple And Noise	200 mVp-p maximum
Average Efficiency	82.96% minimum
Rise Time	100mS maximum at nominal input voltage
Turn On Delay	3 Seconds maximum at nominal input voltage
Protections	Over Current, Over Voltage, Short Circuit Protection
Dimensions	69 (L) * 49 (W) *71.7 (H) mm maximum
Weight	130 g maximum
Output Cord	WIRE: 22AWG/2C 2468 1500mm PLUG: FEMALE JACK PLUG 2.1*5.5*12mm
Operating Temperature	0 °C TO 40 °C
Storage Temperature	-20 °C TO +60 °C
Operating Humidity	20 ~ 85 % RH. NON-CONDENSING
Storage Humidity	5 ~ 95 % RH. NON-CONDENSING

MECHANICAL DRAWINGS:



Stontronics Ltd

Chancerygate Business Centre, Cradock Road, Reading, Berkshire, RG2 0AH.

Tel: +44 (0) 118 931 1199 • Fax: +44 (0) 118 931 1145 • Email: info@stontronics.co.uk • Web: www.stontronics.com

Please Note: Image shown is representative of entire range. Individual PSU image &/or drawings or data sheets available on request.

Stontronics Ltd accepts no responsibility for typographical errors in the production of this leaflet. Product specifications are subject to change without notice.

