


Aluminum Electrolytic, 105C, PEH532, 330 uF, 20%, 400 V, -40/+105C



| Dimensions | |
|------------|---------------|
| D | 30mm +1mm |
| L | 40mm +/-2mm |
| S | 10mm +/-0.1mm |
| LL | 6.3mm +/-1mm |
| F | 2mm +/-0.1mm |

| Packaging Specifications | |
|--------------------------|------|
| Weight: | 39 g |
| Packaging: | Bulk |
| Packaging Quantity: | 100 |

| General Information | |
|---------------------|--|
| Dielectric: | Aluminum Electrolytic |
| Series: | PEH532 |
| Description: | Snap-In, Aluminum Electrolytic |
| RoHS: | Yes |
| Lead: | 2 Pin |
| Notes: | Add 0.5mm To D And 1mm To L For Sleeving |

| Specifications | |
|------------------------|---|
| Capacitance: | 330 uF |
| Capacitance Tolerance: | 20% |
| Voltage DC: | 400 VDC |
| Temperature Range: | -40/+105C |
| Rated Temperature: | 105C |
| Life: | 1500 Hrs (Rated Voltage And Ripple Current At 105C), 2000 Hrs (Rated Voltage At 105C) |
| Resistance: | 340 mOhms (100Hz 20C), 210 mOhms (100kHz 20C) |
| Current: | 1.3 Amps (100Hz 105C), 3.6 Amps (20kHz 40C) |
| Leakage: | 396 uAmps (5min 20C) |