


KEMET Part Number: R75LF22204000K
(75LF22204000K)

Film, Metallized Polypropylene, Commercial Grade, R75L, 0.022 uF, 10%, 560 V, 85C, Lead Spacing = 10mm



Dimensions

L	13mm +0.3mm
H	9mm +0.1mm
T	4mm +0.2mm
S	10mm +/-0.4mm
LL	30mm +5mm
F	0.8mm +/-0.05mm

Packaging Specifications

Packaging:	Bulk, Bag
-------------------	-----------

General Information

Dielectric:	Metallized Polypropylene
Style:	Radial
Series:	R75L
Features:	Pulse
RoHS:	Yes
Lead:	Wire Leads

Specifications

Capacitance:	0.022 uF
Capacitance Tolerance:	10%
Voltage DC:	560 VDC, 336 VDC (105C)
Voltage AC:	250 VAC
Temperature Range:	-55/+105C
Rated Temperature:	85C
Dissipation Factor:	4% 1kHz, 6% 10kHz, 25% 100kHz
Insulation Resistance:	1360 GOhms
Max dVdt:	1,500 V
Inductance:	10 nH