

KEMET Part Number: R75LN41004000K
(75LN41004000K)

Film, Metallized Polypropylene, Commercial Grade, R75L, 1 uF, 10%, 560 V, 85C, Lead Spacing = 22.5mm



Dimensions

L	26.5mm +0.3mm
H	22mm +0.1mm
T	13mm +0.2mm
S	22.5mm +/-0.4mm
LL	30mm +5mm
F	0.8mm +/-0.05mm

Packaging Specifications

Packaging:	Bulk, Bag
Packaging Quantity:	200

General Information

Dielectric:	Metallized Polypropylene
Style:	Radial
Series:	R75L
Features:	Pulse
RoHS:	Yes
Lead:	Wire Leads

Specifications

Capacitance:	1 uF
Capacitance Tolerance:	10%
Voltage DC:	560 VDC, 336 VDC (105C)
Voltage AC:	250 VAC
Temperature Range:	-55/+105C
Rated Temperature:	85C
Dissipation Factor:	0.05% 1kHz, 0.08% 10kHz
Insulation Resistance:	30 GOhms
Max dVdt:	250 V
Inductance:	18 nH