

Keysight Technologies

Extreme Temperature Probing Solutions for Oscilloscope Measurements

Industry's most comprehensive extreme-temperature
chamber testing solutions for oscilloscopes

Data Sheet



Unlocking Measurement Insights

- Passive and active probing solutions for extreme environmental testing
- Supports temperature ranges as wide as -55 to $+150$ °C

Many engineers have a need to monitor their product in an environmental chamber with an oscilloscope probe to verify performance over a wide range of operating temperatures or to determine the cause of failures at high or low temperatures. Until now, testing in extreme temperature ranges required engineers to use probes outside their specified operating temperatures, which can damage probes. Most active or passive probes in the market have a specified operating temperature range anywhere from 0 to 50 °C. However, Keysight Technologies Inc. offers various extreme temperature probing solutions that can be operated over a much wider -40 to $+85$ °C range or even beyond. This allows you to operate the probe head and the supplied probing accessories inside a temperature chamber with the probe pod and oscilloscope located outside the temperature chamber.

For extended temperature testing with more extreme temperature range measurements, Keysight offers the N5450B InfiniiMax extreme-temperature extension cable with the InfiniiMax Series differential probing system, which gives engineers the ability to probe signals at even wider temperature ranges. When used with the Keysight N5381A or N5441A differential solder-in probe head, this solution provides engineers with the widest temperature range coverage of -55 to 150 °C, which is the maximum temperature range specified for automotive-electronics testing.



When accurate and repeatable current measurements inside the chamber are critical over wide temperature ranges, the N2820A/21A high-sensitivity current probe is the best choice, especially for precision current measurement applications. When the user-defined head is used with the N2820A/21A current probe, it provides the industry's highest sensitivity current measurement solution among oscilloscope current probes, going all the way down to 50 μ A with a maximum current range of 5 A operating over the temperature range of -55 to 150 °C.



The N2797A 1.5 GHz single-ended active probe is the industry's first low-cost high-impedance active probe for environmental chamber testing of ICs and electronic devices at temperatures ranging from -40 to $+85$ °C. The probe provides 1.5 GHz of bandwidth and high resistance (1 M Ω) and low capacitance (1 pF) input for low probe loading.



The N7007A 400 MHz passive probe is a low-cost, high impedance passive probe with rugged probe tips for environmental chamber testing from -40 to $+85$ °C. Its large input impedance (10 M Ω @ DC) and wide input voltage range ($1,000$ Vdc + peak AC CATII) makes the probe ideal for a broad range of general purpose extreme temperature applications.



The N7013A is a 70 cm long extreme temperature extension kit compatible with four of Keysight's medium- & high-voltage differential active probes including the N2790A, N2791A, N2792A and N2818A. These probes are typically used in power supply testing applications, as well as testing automotive differential buses including CAN, CAN FD, and FlexRay. With the N7013A extension kit, the extension cables and connection adapters can be extended into the environmental chamber under extreme-temperature conditions ranging from -40 to +85 °C.



This extreme temperature probing solution provides an ideal solution for engineers working with the semiconductor, consumer, wireless mobile devices, automotive electronics, and computer industries who need to validate and characterize their designs while operating within extreme temperature ranges. Keysight now offers the broadest selection of extreme-temperature oscilloscope probing solutions in the market.

There are different bandwidths, temperature ranges and test cycle numbers depending on which probe head/tip you select to use.

| Probes and accessories | Signal measurement type | Max bandwidth | Temperature range | Test cycle numbers |
|---|--------------------------------------|--|-------------------|--------------------|
| N2836A differential solder-in probe head + InfiniiMax III N2803A | Single-ended or differential voltage | 26 GHz | -40 to +85 °C | 1000+ |
| N5441A differential solder-in probe head + InfiniiMax III N280xA or InfiniiMax III+ | Single-ended or differential voltage | 16 GHz | -55 to +150 °C | 250+ |
| N5381A differential solder-in probe head + InfiniiMax II 1169A | Single-ended or differential voltage | 12 GHz | -55 to +150 °C | 250+ |
| N5381B differential solder-in probe head + InfiniiMax II 1169A | Single-ended or differential voltage | 12 GHz | -40 to +85 °C | 1000+ |
| E2677A differential solder-in probe head + InfiniiMax II 1169A | Single-ended or differential voltage | 12 GHz | -25 to +80 °C | 1000+ |
| E2678A differential socket probe head + InfiniiMax II 1169A | Single-ended or differential voltage | 12 GHz | -25 to +80 °C | |
| N5425A ZIF head + N5426A tip + InfiniiMax II 1169A | Single-ended or differential voltage | 12 GHz | -25 to +80 °C | |
| N5425B ZIF head + N5426A tip + InfiniiMax II 1169A | Single-ended or differential voltage | 12 GHz | -40 to +85 °C | 500+ |
| N2797A single-ended active probe | Single-ended voltage | 1.5 GHz | -40 to +85 °C | |
| N7007A passive probe | Single-ended | 400 MHz | -40 to +85 °C | |
| N7013A differential extension kit | Differential | 70 MHz with N2818A, N2792A, N2790A, 25 MHz with N2791A | -40 to +85 °C | |
| N2820A current probe with user defined head and silicon jacketed hook-up cable | Single-ended current | 3 MHz (zoom-out)/500 kHz (zoom-in) | -55 to +150 °C | |

Ordering Information

- For InfiniiMax probe with extension cable + probe head, order one of these configurations below, depending on your probe bandwidth and accessory requirements.

1. **InfiniiMax I probe:** 1130A/31A/32A/34A InfiniiMax I probe amp + N5450B extension cable + E2677A solder-in head or E2678A socketed head
2. **InfiniiMax II probe:** 1168A/69A InfiniiMax II probe amp + N5450B extension cable + N5381A solder-in head or N5425A/26A ZIF head/tip or E2677A solder-in head or E2678A socketed head
3. **InfiniiMax III/III+ probe:** N2800A/01A/02A/03A InfiniiMax III probe amp or N2830A/31A/32A or N7000A/01A/02A/03A, InfiniiMax III+ probe amp + N5450B extension cable + N5441A solder-in head

- N2797A 1.5 GHz single-ended active probe
 - For additional accessories, order the N2798A accessory kit for N2797A active probe. It comes with all the standard accessories of the N2797A.
- N2820A 3 MHz high sensitivity current probe.
- N7013A differential extension cable kit includes one each pair of differential extension cables (70 cm long), hook tip adapters and banana-to-socketed tip adapters for connecting to 0.025" sq pins. Order N7014A for an extra banana-to-socketed tip adapter pair.
- N7007A passive probe comes with retractable hook tips, alligator ground leads and spring ground tip. To reorder the accessories, order N7006A spring ground tip, N7008A retractable hook tip or N7009A alligator ground lead.

For more information on the extreme temperature probing solution, go to www.keysight.com/find/extreme.

To learn more about Keysight's probing solutions, go to www.keysight.com/find/probes.



- N2797A single-ended
- 1.5 GHz
 - 1 MΩ input R
 - -40 to +85 °C



- InfiniiMax + N5450B extension cable + probe head
- Differential & SE
 - 1.5 to 16 GHz
 - 50 kΩ input R
 - -55 to +150 °C



- N2820A/21A high-sensitivity current probe
- Current
 - 3 MHz
 - 1.5 GΩ input R
 - -55 to +150 °C



- N7013A extreme temperature extension kit
- 70 MHz
 - For use with N2790A, N2791A, N2792A or N2818A
 - -40 to +85 °C



- N7007A passive probe
- 400 MHz
 - 10 MΩ input R
 - -40 to +85 °C



www.axistandard.org

AdvancedTCA® Extensions for Instrumentation and Test (AXIe) is an open standard that extends the AdvancedTCA for general purpose and semiconductor test. Keysight is a founding member of the AXIe consortium. ATCA®, AdvancedTCA®, and the ATCA logo are registered US trademarks of the PCI Industrial Computer Manufacturers Group.



www.lxistandard.org

LAN eXtensions for Instruments puts the power of Ethernet and the Web inside your test systems. Keysight is a founding member of the LXI consortium.




www.pxisa.org

PCI eXtensions for Instrumentation (PXI) modular instrumentation delivers a rugged, PC-based high-performance measurement and automation system.

From Hewlett-Packard through Agilent to Keysight

For more than 75 years, we've been helping you unlock measurement insights. Our unique combination of hardware, software and people can help you reach your next breakthrough. **Unlocking measurement insights since 1939.**



1939

THE FUTURE

For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: www.keysight.com/find/contactus

Americas

| | |
|---------------|------------------|
| Canada | (877) 894 4414 |
| Brazil | 55 11 3351 7010 |
| Mexico | 001 800 254 2440 |
| United States | (800) 829 4444 |

Asia Pacific

| | |
|--------------------|----------------|
| Australia | 1 800 629 485 |
| China | 800 810 0189 |
| Hong Kong | 800 938 693 |
| India | 1 800 11 2626 |
| Japan | 0120 (421) 345 |
| Korea | 080 769 0800 |
| Malaysia | 1 800 888 848 |
| Singapore | 1 800 375 8100 |
| Taiwan | 0800 047 866 |
| Other AP Countries | (65) 6375 8100 |

Europe & Middle East

| | |
|----------------|---------------|
| Austria | 0800 001122 |
| Belgium | 0800 58580 |
| Finland | 0800 523252 |
| France | 0805 980333 |
| Germany | 0800 6270999 |
| Ireland | 1800 832700 |
| Israel | 1 809 343051 |
| Italy | 800 599100 |
| Luxembourg | +32 800 58580 |
| Netherlands | 0800 0233200 |
| Russia | 8800 5009286 |
| Spain | 800 000154 |
| Sweden | 0200 882255 |
| Switzerland | 0800 805353 |
| | Opt. 1 (DE) |
| | Opt. 2 (FR) |
| | Opt. 3 (IT) |
| United Kingdom | 0800 0260637 |

For other unlisted countries:
www.keysight.com/find/contactus
 (BP-02-10-16)



www.keysight.com/go/quality
 Keysight Technologies, Inc.
 DEKRA Certified ISO 9001:2015
 Quality Management System

myKeysight

myKeysight

www.keysight.com/find/mykeysight
 A personalized view into the information most relevant to you.

Three-Year Warranty

www.keysight.com/find/ThreeYearWarranty
 Keysight's committed to superior product quality and lower total cost of ownership. Keysight is the only test and measurement company with three-year warranty standard on all instruments, worldwide. And, we provide a one-year warranty on many accessories, calibration devices, systems and custom products.



Keysight Assurance Plans

www.keysight.com/find/AssurancePlans
 Up to ten years of protection and no budgetary surprises to ensure your instruments are operating to specification, so you can rely on accurate measurements.



Keysight Infoline

www.keysight.com/find/service
 Keysight's insight to best in class information management. Free access to your Keysight equipment company reports and e-library.

Keysight Infoline

Keysight Channel Partners

www.keysight.com/find/channelpartners
 Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.

www.keysight.com/find/extreme