








M300 Connectors

Male Cable Connector Contacts

- Crimp barrel meets all crimp guidelines and standards.
- 10A current capacity, resists high vibration and shock.
- Withstands extremes of temperature: -65°C to +175°C.



CONTACTS	WIRE STRIPPING DETAILS							
<p>18-20 AWG</p>  <p>22 AWG</p> 	 <p>18-20 AWG - Ø1.80 max 22 AWG - Ø1.40 max</p> <p>2.00 nominal</p>							
TOOLS								
<p>Recommended Crimp Tool - M22520/2-01 Positioner - Z80-058</p>	<p>Contact Insertion/Removal Tool - Z300-902 See page 12j ➤ Instruction sheets available at www.harwin.com/instructions</p>							
HOW TO ORDER								
<p>SERIES CODE</p> <p>TYPE</p> <table border="1" data-bbox="186 1669 511 1795"> <tr> <td>101</td> <td>18-20 AWG crimp contact</td> </tr> <tr> <td>102</td> <td>22 AWG crimp contact</td> </tr> </table>	101	18-20 AWG crimp contact	102	22 AWG crimp contact	<p>M300 - 10X 00 45</p> <p>FINISH</p> <table border="1" data-bbox="1096 1711 1437 1795"> <tr> <td>45</td> <td>Gold</td> <td></td> </tr> </table>	45	Gold	
101	18-20 AWG crimp contact							
102	22 AWG crimp contact							
45	Gold							

All dimensions in mm.