

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0877159302](#)
Status: **Active**
Overview: PCI Express* Card Edge Connector
Description: 1.00mm Pitch, PCI Express* Connector, 164 Circuits, Nylon 4/6 Glass-filled, Black Housing, Phosphor Bronze, 0.38µm Gold Solder-tail, Lead-Free

Documents:

3D Model	Packaging Specification PK-87715-207 (PDF)
Drawing (PDF)	Test Summary TS-87715-207 (PDF)
Product Specification PS-87715-200 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification


CSA	LR19980
UL	E29179

General

Product Family	Edge Card Connectors
Series	87715
Circuit Size Range	65-200 Circuits
Comments	PCI 16 lanes
Component Type	Edgecard to PCB
Data Rate	8.0 Gbps
Edge Card Thickness	1.57mm
Electrical Model	Yes
High Power Bay (30.0A or more)	No
Orientation	Vertical
Overview	PCI Express* Card Edge Connector
Product Name	PCI Express*
Standard Based	PCIe
UPC	822348683406

Physical

(p)ower-(s)ignal Configuration	164s - 0p
Circuits (Loaded)	164
Circuits (maximum)	164
Color - Resin	Black
Durability (mating cycles max)	50
Entry Angle	Vertical (Top Entry)
Flammability	94V-0
Keying to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	8.693/g
PC Tail Length	2.54mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	1.00mm
Pitch - Termination Interface	1.00mm
Plating min - Mating	0.381µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Temperature Range - Operating	-55°C to +85°C
Termination Interface: Style	Through Hole



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/79/2015 (17
December 2015)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

Search Parts in this Series

[87715 Series](#)

Mates With

PCI Express* Card

Electrical

Current - Maximum per Contact 1.1A
Voltage - Maximum 50V AC (RMS)/DC

Solder Process Data

Duration at Max. Process Temperature (seconds) 010
Lead-free Process Capability WAVE
Max. Cycles at Max. Process Temperature 001
Process Temperature max. C 260

Material Info**Reference - Drawing Numbers**

Electrical Model Document EE-87715-002, EE-87715-011, EE-87715-012,
EE-87715-013, EE-87715-014
Packaging Specification PK-87715-207
Product Specification PS-87715-200
S-Parameter Model SP-87715-002, SP-87715-011, SP-87715-012,
SP-87715-013, SP-87715-014
Sales Drawing SD-87715-901
Signal Integrity Report SI-87715-002
Test Summary TS-87715-207

*PCI Express is a registered trademark of PCI-SIG®.

This document was generated on 06/09/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION