


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0348240125](#)
Status: **Active**
Overview: [Mini50™ Connection Systems](#)
Description: Mini50™ Unsealed Receptacle, Dual Row, Non-Bridged, 12 Circuits, Polarization Option B, Gray

Documents:

3D Model	Application Specification AS-34791-020-CH (PDF)
Drawing (PDF)	Application Specification AS-34791-020-FR (PDF)
Product Specification PS-34791-020 (PDF)	Packaging Specification PK-31301-538 (PDF)
Application Specification AS-34791-020 (PDF)	RoHS Certificate of Compliance (PDF)



General

Product Family	Crimp Housings
Series	34824
Application	Power, Wire-to-Board
Overview	Mini50™ Connection Systems
Polarization	B
Product Name	Mini50™
UPC	887191309477

Physical

Circuits (maximum)	12
Color - Resin	Gray
Gender	Receptacle
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	1.469/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +105°C

Solder Process Data

Lead-free Process Capability	N/A
------------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	AS-34791-020, AS-34791-020-CH, AS-34791-020-FR
Packaging Specification	PK-31301-538
Product Specification	PS-34791-020
Sales Drawing	SD-34824-002

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/79/2015 (17
December 2015)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS
ELV

Green Image
Compliant

Search Parts in this Series

[34824 Series](#)

Mates With

Mini50™ Vertical Headers [34825](#) , Mini50™ Right-Angle Through Hole Header [34826](#) , Mini50™ Right-Angle Surface Mount Header [34897](#)

Use With

CTX50 Unsealed Terminals [560023](#)