

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0465563745](#)
Status: **Active**
Overview: SEARAY* Slim
Description: SEARAY* Slim Plug, 120 Circuits, 7.00mm Unmated Height, 4 Rows, with Pegs, Solder Charge™ Lead-Free

Documents:

[3D Model](#) [Packaging Specification PK-45970-002 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

General

Product Family PCB Headers
 Series 46556
 Application Board-to-Board, Signal
 Electrical Model Yes
 Overview [SEARAY* Slim](#)
 Product Name SEARAY*
 UPC 883906482626

Physical

Breakaway No
 Circuits (Loaded) 120
 Circuits (maximum) 120
 Color - Resin Black
 Durability (mating cycles max) 100
 First Mate / Last Break No
 Flammability 94V-0
 Glow-Wire Compliant No
 Guide to Mating Part Yes
 Keying to Mating Part Yes
 Lock to Mating Part None
 Material - Metal Copper Alloy
 Material - Plating Mating Gold
 Material - Plating Termination Tin
 Material - Resin High Temperature Thermoplastic
 Net Weight 3.074/g
 Number of Rows 4
 Orientation Vertical
 PCB Locator Yes
 PCB Retention Yes
 PCB Thickness - Recommended 1.60mm
 Packaging Type Embossed Tape on Reel
 Pitch - Mating Interface 1.27mm
 Pitch - Termination Interface 1.27mm
 Plating min - Mating 0.762µm
 Polarized to Mating Part Yes
 Polarized to PCB Yes
 Robotic Placement Pick and Place Cap
 Shrouded No
 Stackable No
 Surface Mount Compatible (SMC) Yes
 Temperature Range - Operating -55°C to +125°C
 Termination Interface: Style Surface Mount



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/21/2016 (20 June
 2016)

Halogen-Free

Status

Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

Search Parts in this Series

[46556](#) Series

Mates With

[46557](#) SEARAY* Slim Receptacles

Unmated Height 7.00mm

Electrical

Current - Maximum per Contact 2.7A
Voltage - Maximum 240V AC

Solder Process Data

Duration at Max. Process Temperature (seconds) 020
Lead-free Process Capability REFLOW
Max. Cycles at Max. Process Temperature 003
Process Temperature max. C 260

Material Info

Reference - Drawing Numbers

Electrical Model Document EE-45970-010
Packaging Specification PK-45970-002
S-Parameter Model SP-45970-010
Sales Drawing SD-46556-001
Symbol/Footprint Data SYM-46556-3745

*SEARAY is a trademark of Samtec, Inc.

This document was generated on 07/18/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION