

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0334722006](#)
Status: **Active**
Overview: [MX150™ Sealed and Unsealed Connector System](#)
Description: MX150™ Sealed Female Connector, Dual Row, 20 Circuits, Polarization A, with Connector Position Assurance, Black

Documents:

3D Model	Packaging Specification PK-31300-903 (PDF)
Drawing (PDF)	Packaging Specification PK-33472-001 (PDF)
Product Specification PS-33472-000 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Housings
Series	33472
Application	Power, Wire-to-Wire
Comments	with Connector Position Assurance (CPA)
More Detailed Tech Information	http://uscar.org/guest/teams/10/Electrical-Wiring-Component-Applications-Partnership
Overview	MX150™ Sealed and Unsealed Connector System
Product Name	MX150™
UPC	822348390090

Physical

Circuits (maximum)	20
Color - Resin	Black, Natural
Gender	Female
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Modified Polystyrene Alloy
Net Weight	21.740/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +125°C

Solder Process Data

Lead-free Process Capability	N/A
------------------------------	-----

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-31300-903, PK-33472-001
Product Specification	PS-33472-000
Sales Drawing	SD-33472-0001, SD-33472-0002



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/21/2016 (20 June 2016)

Halogen-Free

Status

Not Relevant

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

Not Relevant

Compliant

Search Parts in this Series

[33472 Series](#)

Mates With

[33482 Male Dual Row Sealed Connector](#)

Use With

[33012 MX150™ Female Terminal](#),
[34345-0001 MX150™ Cavity Plug Sealed](#)