


59630 Sensor with Integral Float Actuator

RoHS



Dimensions

Dimensions in mm (inch)



Schematics	Switch Type
Black Black	1 and 2
Black Blue White	3
Black Black	4

Description

The 59630 is a reed level sensor with integral float actuator and an M8 x 1.25mm pitch thread with a choice of normally open, normally open high voltage, normally closed or change over contacts. It is capable of switching up to 265Vac/300Vdc at 10VA. It is ideally suited to liquid and air conditioning condensate and industrial process control applications.

Features

- Sensor with integral blown polypropylene float, with integral magnet
- Sensor operates when float rises from end stop position
- Choice of contacts
- Choice of connector and cable length options

Benefits

 Hermetically sealed, magnetically operated contacts continue to operate long after optical and other technologies fail due to contamination

- · No standby power required
- Simple installation with M8 thread and nut

Applications

- · Liquid level control
- · Air conditioning systems
- Industrial Process Control



59630 Sensor with Integral Float Actuator

Electrical Ratings


Contact Type			Normally Open	Normally Open High Voltage	Change Over	Normally Closed
Switch Type		1	2	3	4	
Contact Rating ¹		VA/Watt - max.	10	10	5	10
Voltage ⁴	Switching ² Breakdown ³	Vdc - max. Vac - max. Vdc - min.	200 140 250	300 265 400	175 120 200	200 120 250
Current ⁴	Switching ² Carry	Adc - max. Aac - max. Adc - max.	0.5 0.35 1.2	0.4 0.30 1.4	0.25 0.18 1.5	0.5 0.18 1.2
Resistance ⁵	Contact, Initial Insulation	Ω - max. Ω - min.	0.2 10 ¹⁰	0.2 10 ¹⁰	0.2 10 ⁹	0.2 10 ¹⁰
Capacitance	Contact	pF - typ.	0.3	0.2	0.3	0.3
Temperature	Operating	°C	-40 to +105	-20 to +105	-40 to +105	-40 to +105
Product Characteristics						
Operate Time ⁶		ms - max.	1.0	1.0	3.0	3.0
Release Time ⁶ ms - max.		ms - max.	1.0	1.0	3.0	3.0
Shock 7	11ms ½ sine	G - max.	100	100	50	50
Vibration ⁷	50-2000 Hz	G - max.	30	30	30	30

Notes:

- 1. Contact rating Product of the switching voltage and current should never exceed the wattage rating. Contact Littelfuse for additional load/life information.
- 2. When switching inductive and/or capacitive loads, the effects of transient voltages and/or currents should be considered. Refer to Application Notes AN108A and AN107 for details.
- 3. Breakdown Voltage per MIL-STD-202, Method 301.
- 4. Electrical Load Life Expectancy Contact Littelfuse with voltage, current values along with type of load.
- 5. This resistance value is for 11.81mm wire length. Resistance changes when wire lengthens.
- 6. Operate (including bounce)/Release Time per EIA/NARM RS-421-A, diode suppressed coil (Coil II).
- 7. Shock and Vibration per EIA/NARM RS-421-A and MIL-STD-202.
- 8. For custom modifications to the wire length or size, or adding a special connector, please contact Littelfuse.

Activation

Using sensor with float magnet orientated is illustrated





59630 Sensor with Integral Float Actuator


Cable Length Specification

Cable Type: 24 AWG 7/32 PVC 105°C UL1430/UL1569		
Select Option	Cable Length mm (inch)	
02	300 (11.81)	

Termination Specification

Termination Options				
Select Option	Description (Two-wire versions illustrated)			
А	Tinned leads (6.4±0.76)mm			
F	Untinned leads (6.4±0.76)mm			
Е	JST type XHP 2.5mm pitch			

Part Numbering System



Packaging

Packaging Option	Packaging Specification	Quantity	Quantity & Packaging Code	Taping Width
Bulk	Bulk	500	N/A	N/A