


ENERGIZER NO. EN539

J - 6V



Industry Standard Dimensions in mm (inches)



NOT INTENDED FOR RETAIL TRADE

Chemical System: Alkaline
 Zinc-Manganese Dioxide (Zn/MnO₂)
 (No Added Mercury or Cadmium)

Designation: ANSI-1412AP, IEC-4LR61

Battery Voltage: 6.0 Volts

Operating Temp: -18°C to 55°C (0°F to 130°F)

Average Capacity: 625 mAh (to 0.8 volts/cell)
 (Rated capacity at 25 mA continuous drain.)

Average Weight: 30 grams (1.1 oz.)

Volume: 15.4 cubic centimeters (0.9 cubic inch)

Cell: Four No. 3-0316 in series


Jacket: Plastic

Terminal: Flat Contacts


ELECTRONIC APPLICATION
 330 ohms - 24 hours/day



ELECTRONIC APPLICATION
 6,800 ohms - 24 hours/day



CONSTANT CURRENT DISCHARGE
 Typical Service



CONSTANT CURRENT APPLICATION
 9 mA @ 20°C



Important Notice

This data sheet contains information specific to batteries manufactured at the time of its publication.

Contents herein do not constitute a warranty.

Copyright © Eveready Battery Co. - All rights reserved