

General Information

Extended Product Type:	ZK2.5-PE-3P
Product ID:	1SNK705151R0000
EAN:	3472597051517
Catalog Description:	ZK2.5-PE-3P PI-Spring clamp Terminal Block - Ground - Green Yellow
Long Description:	Improve the safety of your installation in the event of a short-circuit thanks to our screwless rail contact: - Rail contact non operator dependent, - Performances above the requirements of the IEC 60947-7-2 terminal block standard, - Secured snap on or off the rail, - Profile aligned with ZK2.5-3P.

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks » SNK Series

Ordering

Minimum Order Quantity:	20 piece
Customs Tariff Number:	85369010
Color:	Green-Yellow

Dimensions

Product Net Height:	71.2 mm
Product Net Length:	40.3 mm
Product Net Depth:	40.3 mm
Product Net Weight:	11.9 g
Product Net Width:	5.2 mm

Technical

Spacing:	5.2 mm
Connection Type:	PI Spring
Function:	Ground
Number of Levels:	1
Connecting Capacity Main Circuit:	Spring Clamp / Flexible 1x 0.22 ... 2.5 mm ² Spring Clamp / Rigid 1x 0.2 ... 4 mm ² Spring Clamp / With Insulated Ferrule 1x 0.22 ... 2.5 mm ² Spring Clamp / Without Insulated Ferrule 1x 0.22 ... 2.5 mm ²
Gauge Type:	A2 / 2.3 mm Dia.
Rated Short-time Withstand Current (I_{cw}):	for 1 s 300 A
Rated Impulse Withstand Voltage (U_{imp}):	8000 V
Dielectric Test Voltage:	2200 V
Pollution Degree:	3
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Mounting on DIN Rail:	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Wire Stripping Length:	11.0 mm
Rated Cross-Section:	2.5 mm ²

Technical UL/CSA

Connecting Capacity Main Circuit UL/CSA:	Spring Clamp / Rigid 1x 26 ... 12 AWG Spring Clamp / With Insulated Ferrule 1x 26 ... 14 AWG Spring Clamp / Without Insulated Ferrule 1x 26 ... 14 AWG
Connecting Capacity UL/CSA:	Stranded 12 AWG
Flammability According to UL94:	V0

Environmental

Resistance to Vibrations acc. to IEC 60068-2-6:	Compliant
RoHS Status:	Following EU Directive 2011/65/EC
Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C

Certificates and Declarations (Document Number)

Instructions and Manuals:	1SNK160027C0201
----------------------------------	-----------------

ATEX Certificate:	1SND162009A1701
BV Certificate:	1SND162013A0202
CB Certificate:	1SND162017A0200
CSA Certificate:	1SND162014A0203
cUL Certificate:	1SND162012A0203
Data Sheet, Technical Information:	1SNK162020D0201
Declaration of Conformity - CE:	1SND225112U1000
DNV Certificate:	1SND162023A0200
EAC Certificate:	1SND161010A1100
RoHS Information:	1SND230535F0201

Classifications

ETIM 4:	EC000901 - Ground terminal block
ETIM 5:	EC000901 - Ground terminal block
ETIM 6:	EC000901 - Ground terminal block
Object Classification Code:	X

Container Information

Package Level 1 Width:	54 mm
Package Level 1 Length:	145 mm
Package Level 1 Height:	42 mm
Package Level 1 Gross Weight:	0.258 kg
Package Level 1 EAN:	3472597051517
Package Level 2 Units:	640 piece
Package Level 2 Width:	300 mm
Package Level 2 Length:	400 mm
Package Level 2 Height:	200 mm
Package Level 2 Gross Weight:	8.256 kg
Package Level 3 Units:	30720 piece
Product Packing Type:	Box
Package Level 1 Units:	20 piece

