

General Information

Extended Product Type:	NF62E-13
Product ID:	1SBH137001R1362
EAN:	3471523100534
Catalog Description:	NF62E-13 100-250V50/60HZ-DC Contactor Relay
Long Description:	NF contactor relays are used for switching auxiliary and control circuits. NF contactor relays include an electronic coil interface accepting a wide control voltage $U_c \text{ min.} \dots U_c \text{ max.}$ Only four coils cover control voltages between 24...500 V 50/60 Hz or 20...500 V DC. NF contactor relays can manage large control voltage variations. One coil can be used for different control voltages used worldwide without any coil change. NF contactor relays have built-in surge protection and do not require additional surge suppressors. - Poles: 8-pole contactor relays with a non-removable front-mounted auxiliary contact block (mechanically-linked auxiliary contacts compliant with Annex L of IEC 60947-5-1 and including the "Mechanically Linked" symbol on the contactor relay side) - Control Circuit: AC or DC operated - Accessories: a wide range of Accessories is available.

Categories

Products » Low Voltage Products and Systems » Control Products » Contactors » Block Contactors

Ordering

Minimum Order Quantity:	1 piece
Customs Tariff Number:	85369085
EAN:	3471523100534

Dimensions

Product Net Depth:	110.5 mm
Product Net Height:	86 mm
Product Net Weight:	0.320 kg
Product Net Width:	45 mm

Container Information

Package Level 1 Width:	87 mm
Package Level 1 Length:	113 mm
Package Level 1 Height:	47 mm
Package Level 1 Gross Weight:	0.32 kg
Package Level 1 EAN:	3471523100534
Package Level 2 Units:	36 piece
Package Level 2 Width:	250 mm
Package Level 2 Length:	300 mm
Package Level 2 Height:	315 mm
Package Level 3 Units:	864 piece
Package Level 1 Units:	1 piece

Technical

Number of Auxiliary Contacts NO:	6
Number of Auxiliary Contacts NC:	2
Standards:	IEC 60947-5-1 and EN 60947-5-1, UL 508, CSA C22.2 N°14
Rated Operational Voltage:	Auxiliary Circuit 690 V Main Circuit 690 V
Rated Frequency (f):	Auxiliary Circuit 50 / 60 Hz
Conventional Free-air Thermal Current (I_{th}):	acc. to IEC 60947-5-1, $q = 40 \text{ }^\circ\text{C}$ 16 A
Rated Operational Current AC-15 (I_e):	(220 / 240 V) 4 A (24 / 127 V) 6 A (400 / 440 V) 3 A (500 V) 2 A (690 V) 2 A
Rated Short-time Withstand Current (I_{cw}):	for 0.1 s 140 A for 1 s 100 A
Maximum Electrical Switching Frequency:	AC-15 1200 cycles per hour DC-13 900 cycles per hour
Rated Operational Current DC-13 (I_e):	(110 V) 0.55 A / 60 W (125 V) 0.55 A / 69 W (220 V) 0.27 A / 60 W (24 V) 6 A / 144 W

	(250 V) 0.27 A / 68 W (400 V) 0.15 A / 60 W (48 V) 2.8 A / 134 W (500 V) 0.13 A / 65 W (600 V) 0.1 A / 60 W (72 V) 1 A / 72 W
Rated Insulation Voltage (U_i):	acc. to UL/CSA 600 V acc. to IEC 60947-5-1 and VDE 0110 (Gr. C) 690 V
Rated Impulse Withstand Voltage (U_{imp}):	6 kV
Maximum Mechanical Switching Frequency:	6000 cycles per hour
Rated Control Circuit Voltage (U_c):	50 Hz 100 ... 250 V 60 Hz 100 ... 250 V DC Operation 100 ... 250 V
Operate Time:	Between Coil De-energization and NC Contact Closing 13...98 ms Between Coil De-energization and NO Contact Opening 11...95 ms Between Coil Energization and NC Contact Opening 38...90 ms Between Coil Energization and NO Contact Closing 40...95 ms
Connecting Capacity Auxiliary Circuit:	Flexible with Ferrule 1/2x 0.75 ... 2.5 mm ² Flexible with Insulated Ferrule 1x 0.75 ... 2.5 mm ² Flexible with Insulated Ferrule 2x 0.75 ... 1.5 mm ² Rigid 1/2x 1...2.5 mm ²
Connecting Capacity Control Circuit:	Flexible with Ferrule 1/2x 0.75 ... 2.5 mm ² Flexible with Insulated Ferrule 1x 0.75 ... 2.5 mm ² Flexible with Insulated Ferrule 2x 0.75 ... 1.5 mm ² Rigid 1/2x 1 ... 2.5 mm ²
Wire Stripping Length:	Auxiliary Circuit 10 mm Control Circuit 10 mm
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Auxiliary Terminals IP20 acc. to IEC 60529, IEC 60947-1, EN 60529 Coil Terminals IP20
Terminal Type:	Screw Terminals

Environmental

Climatic Withstand:	Category B according to IEC 60947-1 Annex Q
Maximum Operating Altitude Permissible:	3000 m
Resistance to Vibrations acc. to IEC 60068-2-6:	5 ... 300 Hz 4 g closed position / 2 g open position
Resistance to Shock acc. to IEC 60068-2-27:	Closed, Shock Direction: B1 25 g Open, Shock Direction: B1 5 g Shock Direction: A 30 g Shock Direction: B2 15 g Shock Direction: C1 25 g Shock Direction: C2 25 g
RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2008 Q1
Ambient Air Temperature:	Close to Contactor for Storage -60...+80 °C Near Contactor for Operation in Free Air -40 ... +70 °C

Technical UL/CSA

Tightening Torque UL/CSA:	Auxiliary Circuit 11 in·lb Control Circuit 11 in·lb
----------------------------------	--

Certificates and Declarations (Document Number)

Instructions and Manuals:	1SBC101027M6801
ABS Certificate:	ABS_15-GE1349500-PDA_90682247
CB Certificate:	CB_SE_70920A1M2
CCC Certificate:	CCC_2011010303465426
Data Sheet, Technical Information:	1SBC101432D0201
Declaration of Conformity - CE:	1SBD250005U1000
DNV Certificate:	DNV_E11683
EAC Certificate:	EAC_RU C-FR ME77 B01006
GL Certificate:	GL_3786612HH
GOST Certificate:	GOST_POCCFR.ME77.B06804.pdf
LR Certificate:	LRS_C1400038
RINA Certificate:	RINA_ELE084013XG
RMRS Certificate:	RMRS_1300132124
RoHS Information:	1SBD251014E1000
UL Certificate:	UL_20130206-E252354-2-1
UL Listing Card:	UL_E252354

Classifications

ETIM 4: EC000196 - Contactor relay

ETIM 5: EC000196 - Contactor relay

ETIM 6: EC000196 - Contactor relay

UNSPSC: 39121500

Object Classification Code: K

