

**KEMET Part Number: PME264NE6100MR30**  
(P264EL104M660A)

Film, Metallized Paper, Safety, PME264/P264, 0.1 uF, 20%, 1,500 V, 660 V, 85C, Lead Spacing = 25.4mm



**Dimensions**

Dimension	Value
L	30.5mm MAX
H	22mm MAX
T	15.3mm MAX
S	25.4mm +/-0.5mm
LL	30mm +5mm
F	1mm NOM

**Packaging Specifications**

<b>Packaging:</b>	Bulk
<b>Packaging Quantity:</b>	75

**General Information**

<b>Dielectric:</b>	Metallized Paper
<b>Style:</b>	Radial
<b>Series:</b>	PME264/P264
<b>Features:</b>	Pulse
<b>RoHS:</b>	Yes
<b>Lead:</b>	Wire Leads
<b>Approvals:</b>	ENEC, UL, cUL
<b>Construction:</b>	Molded

**Specifications**

<b>Capacitance:</b>	0.1 uF
<b>Capacitance Tolerance:</b>	20%
<b>Voltage DC:</b>	1500 VDC
<b>Voltage AC:</b>	660 VAC
<b>Temperature Range:</b>	-40/+85C
<b>Rated Temperature:</b>	85C
<b>Dissipation Factor:</b>	1.3% 1kHz
<b>Insulation Resistance:</b>	12 GOhms
<b>Max dVdt:</b>	600 V
<b>Safety Class:</b>	X2