

**KEMET Part Number: PME261JB5220KR30**  
(P561QM223K500A)

Capacitor, Film, Metallized Paper, 0.022 uF, +/-10% Tol, -40/+100C, General Purpose, 1000 VDC@85C, Lead Spacing=15.2 mm



**Dimensions (mm)**

Symbol	Dimension	Tolerance
L	18.5	MAX
H	13	MAX
T	7.3	MAX
S	15.2	+/-0.4
LL	30	+5
F	0.8	+/-0.05

**Packaging Specifications**

<b>Package Kind:</b>	Bulk
<b>Package Quantity:</b>	400

**General Information**

<b>Supplier:</b>	KEMET
<b>Dielectric:</b>	Metallized Paper
<b>Application:</b>	General Purpose
<b>Sub Application:</b>	DC or Low Frequency Pulse
<b>Style:</b>	Radial Molded
<b>Lead Form:</b>	Wire Leads
<b>Features:</b>	Pulse
<b>RoHS:</b>	Yes

**Specifications**

<b>Capacitance:</b>	0.022 uF
<b>Voltage:</b>	1000 VDC
<b>Tolerance:</b>	+/-10%
<b>Voltage AC:</b>	500 VAC
<b>Rated Temperature:</b>	85C
<b>Temperature Range:</b>	-40/+100C
<b>Dissipation Factor @ 1 kHz:</b>	1.3%
<b>Insulation Resistance:</b>	12 GOhm
<b>Maximum dVdT:</b>	2000 v/us
<b>Miscellaneous:</b>	AC Operation: 70C MAX