

111-01699



Article Number: 111-01699

Description: High-Temp. Cable Tie, 7.9" Long, 100lb Tensile Strength, PAEK, Beige, 100/pkg

Base Data	Local Order Number	111-01699
	Type	PAT100L
	Color	Beige (BGE)
	Features and benefits	<ul style="list-style-type: none"> • Very high heat resistance up to 200°C (392°F). • PAEK material has 2X higher tensile strength than nylon. • PAEK material offers very good chemical resistance against hydrocarbons.
	Quantity Per	bag
	Product Description	HellermannTyton PAEK cable ties offer very high temperature resistance for use in demanding applications such as in engine compartments, near exhaust, and in enclosed industrial cabinets. The PAEK ties are inside serrated and feature a high performance design that, along with the material, offer extremely high tensile strength for tough applications.
	Short Description	High-Temp. Cable Tie, 7.9" Long, 100lb Tensile Strength, PAEK, Beige, 100/pkg
Product Dimensions	Minimum Tensile Strength (Imperial)	100.0lbs
	Minimum Tensile Strength (Metric)	445.0N
	Length L (Imperial)	7.9"
	Length L (Metric)	200.7mm
	Width W (Imperial)	0.33"
	Width W (Metric)	8.0mm
	Bundle Diameter Min. (Imperial)	0.06"
	Bundle Diameter Min. (Metric)	1.5mm
	Bundle Diameter Max. (Imperial)	2.0"
	Bundle Diameter Max. (Metric)	50.8mm
Material and Specifications	Material	Polyaryletherketone (PAEK)
	Material Shortcut	PAEK

111-01699



Material and Specifications	Flammability	UL 94 V0
	Operating Temperature	-67°F to +392°F (-55°C to +200°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	100
	Package Quantity (Metric)	100
	Customs Number(Schedule B)	3926909987