

FINE-L-KOTE LED

2120

Product Description

Fine-L-Kote[™] LED is specifically designed and formulated for light emitting diode applications, where a completely transparent silicone coating is required to provide a tough, protective coating. Fine-L-Kote[™] LED provides maximum flexibility for extreme temperatures on the flex and rigid circuitry found on LED displays. Cured coatings are hydrolytically stable and retain their physical electrical properties after high temperature and humidity exposure. Fine-L-Kote[™] LED will not stress delicate circuit components, and meets the performance parameters (without UV traceability) of MIL-I-46058C, Type SR.

Features / Benefits

- Silicone coating transparent to visible wavelengths, will not block or change light intensity or wavelength
- Extends component life by protecting against adverse environments
- Good insulation properties help with circuit insulation characteristics, excellent flexibility minimizes thermal stress
- Resists moisture, salt, fungus, corrosive vapors, and severe environments
- Engineered to withstand heat generated by electronic circuitry as well as climatic temperature extremes
- Compliant to IPC-CC-830A
- Room temperature cure
- RoHS compliant

Applications

- LED Displays and controls
- Data Communications
- Instrumentation
- Automotive Manufacturing
- Marine Manufacturing
- Process Control

Performance

•	Moisture Resistance	Excellent
•	Removability	Excellent
•	Ease of Repair	Excellent
•	Flexibility	Excellent
•	Adhesion	Excellent
•	Abrasion Resistance	Fair
•	Solvent Resistance	Good

Fine-L-Kote[™] LED is generally compatible with most materials found on printed circuit boards. As with any chemical product, product/component compatibility must be determined on a non-critical area prior to use.

Typical Product Data and Physical Properties

Usable Temp. Range	(-	85°F to 390°F)		
of Cured Coatings	(-	(-65°C to 200°C)		
Tack Free Time		15 min.		
Curing Conditions: Full Cure 24 Hours @ 77°F (25°C)				
(@ 80% R.H.)	or 8 Hour	rs @ 170° (77°C)		
Specific Gravity		0.93		
(Water=1) @ 68°F				
Viscosity (cps @ 77°F)		$65 \pm 5 \text{ cps}$		
Flash Point (TCC)		53°F		
Volume Resistivity		1.5×10^{16}		
(ohm/cm)				
Dielectric Breakdown (v	olts/mil)	1100		
Thermal Conductivity		2.9 x 10 ⁻⁴		
(Cal-cm/sec-cm ² -°C)				
Coefficient of Thermal Expansion (in/in/°C)		2.1 x 10 ⁻⁴		
VOC* Content:				
CARB	56.3%			
SCAQMD	570 g/L			
Federal	56.3%			
RoHS Compliant		Yes		

Usage Instructions

For industrial use only. Read MSDS carefully prior to use. Before applying Fine-L-Kote[™] conformal coatings, clean circuit boards to remove contamination and allow to dry. Cleaning may be performed with Techspray G3, E-LINE[™] and Precision-V defluxers.

SPRAY APPLICATION:

Apply top to bottom, allowing coating to flow evenly around components. Rotate PCB 90° and repeat application. Rotate and apply coating two additional times, then allow board to cure. If additional thickness is desired, apply additional coatings. When using liquid spray with automatic dispensing equipment, adjustments may be required in application rate and viscosity.

DIP APPLICATION:

Using automatic equipment or hand immersion technique, slowly immerse PCB into the coating and remove slowly. Use an average rate of approximately 1 foot per minute. After allowing the board to cure, process may be repeated to achieve desired thickness.

BRUSH APPLICATION:

Evenly apply coating to areas desired at thickness required. Allow time for curing before reapplying to achieve a thick coating. Use WonderMASK to protect components during conformal coating process. After application, cured Fine-L-Kote[™] may be removed using Techspray Conformal Coating Removal Pen (2510-N or 2510-P).

Environmental Impact Data

ENVIRONMENTAL IMPACT DATA						
CFC	0.0%	VOC	56.3%			
HCFC	0.0%	HFC	0.0%			
Cl. Solv.	0.0%	ODP	0.00			

CFC, HCFC, CL. SOLV., VOC, and HFC numbers shown are the content by weight. Ozone depletion potential (ODP) is determined in accordance with the Montreal Protocol and U.S. Clean Air Act of 1990. The ODP of this product is 0.0. It is the sum of the ODP of the substances that may contribute to the depletion of stratospheric ozone, based upon the weight of each substance in the product's formulation.

Packaging and Availability

Fine-L-Kote LED is available in the following sizes:

2120-P	1 Pint Liquid
2120-G	1 Gallon Liquid
2120-5G	5 Gallon Liquid

Environmental Policy

Techspray® is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

Resources

Techspray® products are supported by a global sales, technical and customer services resources.

For additional technical information on this product or other Techspray® products in the United States, call the technical sales department at 800-858-4043, email tsales@techspray.com or visit our web site at: www.techspray.com.

North America

Techspray 8125 Cobb Center Drive Kennesaw, GA 3052 800-858-4043 email: tsales@techspray.com

Europe

ITW Contamination Control BV Saffierlaan 5 2132 VZ Hoofddorp The Netherlands +31 88 1307 400 email: info@itw-cc.com

Countries Outside US

Call to locate a distributor in your country.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray® be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.