

KEMET Part Number: PME261EC6100KR30
(P561CE104K300A)

Capacitor, Film, Metallized Paper, 0.1 uF, +/-10% Tol, -40/+100C, General Purpose, 630 VDC@85C, Lead Spacing=20.3 mm



Dimensions (mm)		
Symbol	Dimension	Tolerance
L	24	MAX
H	14	MAX
T	7.6	MAX
S	20.3	+/-0.4
LL	30	+5
F	0.8	+/-0.05

Packaging Specifications	
Package Kind:	Bulk
Package Quantity:	250

General Information	
Supplier:	KEMET
Dielectric:	Metallized Paper
Application:	General Purpose
Sub Application:	DC or Low Frequency Pulse
Style:	Radial Molded
Lead Form:	Wire Leads
Features:	Pulse
RoHS:	Yes

Specifications	
Capacitance:	0.1 uF
Voltage:	630 VDC
Tolerance:	+/-10%
Voltage AC:	300 VAC
Rated Temperature:	85C
Temperature Range:	-40/+100C
Dissipation Factor @ 1 kHz:	1.3%
Insulation Resistance:	12 GOhm
Maximum dVdT:	900 v/us
Miscellaneous:	AC Operation: 70C MAX