

CHERRY JK-0700EU



Models may vary from the image shown

Compact Keyboard for Professional Use:

CHERRY JK-0700 is advanced CHERRY technology in a compact size. Modern, flat compact design with soft and quiet keys.

Key Benefits

- Flat and compact professional keyboard with quiet, short stroke keys
- Scissor technology: Up to 10 million key actuations
- Adjustable cable routing from the casing (left/center/right)
- Plug & Play via USB connection
- Energy Saving technology
- Optimized for professional use in the office
- Two-tone key labeling

Technical Data: Housing Color: Black

Key Color: Black

Weight (product):

Approx. 345 g /.76 lbs

Total Weight (with packaging): Approx. 488 g / 1.07 lbs.

Cable Length: Approx. 1.80 m / Approx. 5.91 ft.

Current Consumption: Max. 200 mA

Operating Temperature:

0° C to 50° C / 32° F to 122° F

Storage Temperature:

-20°C to 60°C / -4° F to 140° F

Interface: USB

Product Approvals:

C-Tick	C
CE	CE
FCC	F©
UL	UL

System Requirements: USB connection

Delivery Volume:

CHERRY JK-0700 Operating instructions in hard copy

Dimensions (product):

Approx. 305 x 146 x 15 mm Approx. 12.00" x 5.74" x .59"

Packaging Dimensions :

Approx. 350 x 146 x 25 mm Approx. 13.7" x 5.7" x .98"

Reliability:

MTBF (90) > 80,000 hours

Keyboard:

- Key technology: SX (Scissor Switch)
- Service life, standard key: > 10 million key operations
- Inscription technology: Laser
- Inscription layout: Standard
- Number of Keys: 88

Packaging Unit:

Number of products in the master package: 20 Number of master packages per pallet: 24

Warranty:

2 years



Model:

Service Design	Product Name	Order Number	EAN Code
Light Use	CHERRY KC 4000	JK-0700EU	4025112078156

(Possible country/layout versions, others available on request)

Cherry Americas, LLC 11200 88th Avenue Pleasant Prairie, WI 53158 USA Phone: 262.942.6508 Internet: www.cherryamericas.com

E-Mail: mailto:keyboardsupport@cherryamericas.com

The manufacturer accepts no liability for errors or non-availability, and reserves the right to change specifications without prior notice. Technical data relates to product specifications only. Features may differ from those described. Only drawings combined with product specifications shall be deemed binding.