

CY LSZH / BS EN 50525-3-11

Multiconductor Screened Flexible Control Cable

pro-POWER

RoHS
Compliant



Application:

For installation where fire, smoke emission and toxic fumes create a potential threat to life and equipment. Used as interconnecting cable for measuring, controlling or regulation in control equipment for assembly and production lines, conveyors and for computer units. Suitable for fixed installations or for flexible use when temporarily moved, and in conditions of medium mechanical stress. Can be used outdoors when protected, and in dry or damp conditions indoors.

Construction:

Conductor:

Class 5 flexible copper conductor according to BS EN 60228 (previously BS 6360)

Insulation:

Halogen Free Type TI6 according to BS EN 50363

Binding Tape:

PET (Polyester Tape)

Screen:

TCWB (Tinned Copper Wire Braid)

Sheath:

LSZH (Low Smoke Zero Halogen) Type TM7 according to BS EN 50363-8

Cable Standards

Generally to BS EN 50525-3-11, BS EN/IEC 60754-1, BS EN/IEC 60332-1-2

Characteristics:

Voltage Rating (Uo/U)

300/500V

Temperature Rating:

Installation : -15°C to +70°C

Operating : -30°C to +70°C

Minimum Bending Radius:

Fixed : 6 × overall diameter

Flexed : 15 × overall diameter

CY LSZH / BS EN 50525-3-11

Multiconductor Screened Flexible Control Cable

pro-POWER

Core Identification:

Number Coded Cores

Black with White numbers

2 Cores Black

3 and 4 Cores to included Green/Yellow

Sheath Colour:

Grey

Dimensions:

Part Number	No. of Cores	Nominal Cross Sectional Area mm ²	Nominal Overall Diameter mm	Nominal Weight Kg/Km
PP000488	2	0.75	6.1	45
PP000489		1	6.3	57
PP000490		1.5	7.3	75
PP000491	3	0.75	6.4	63
PP000492		1	6.6	73
PP000493		1.5	7.7	95
PP000494	4	0.75	6.9	89
PP000495		1	7.1	86
PP000496		1.5	8.4	118

Conductors:

Class 5 Flexible Copper Conductors for Single Core and Multi-Core Cables

Nominal Cross Sectional Area mm ²	Maximum Resistance of Conductor at 20°C
0.75	26
1	19.5
1.5	13.3

Electrical Characteristics:

Current Carrying Capacity at 30°C

Nominal Cross Sectional Area mm ²	Current Rating Amps
0.75	12
1	15
1.5	18

CY LSZH / BS EN 50525-3-11

Multiconductor Screened Flexible Control Cable



Part Number Table

Description	No. of Cores	Reel Length	Part Number
CY LSZH / BS EN 50525-3-11 Multiconductor Screened Flexible Control Cable	2	100m	PP000488
			PP000489
			PP000490
	3		PP000491
			PP000492
			PP000493
	4		PP000494
			PP000495
			PP000496

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of the Group. © Premier Farnell Limited 2016.