

Ceramic, Electro Static Discharge, ESD-FlexTerm-AUTO, 4700 pF, 10%, 100 V, 0603, COG, SMD, MLCC, FT-CAP, Temperature Stable, Electro Static Discharge, Automotive Grade



Dimensions	
L	1.6mm +/-0.17mm
W	0.8mm +/-0.15mm
T	0.8mm +/-0.15mm
S	0.58mm MIN
B	0.45mm +/-0.15mm

Packaging Specifications	
Packaging:	T&R, 180mm, Paper Tape
Packaging Quantity:	4000

General Information	
Style:	SMD Chip
Series:	ESD-FlexTerm-AUTO
Chip Size:	0603
Description:	SMD, MLCC, FT-CAP, Temperature Stable, Electro Static Discharge, Automotive Grade
Features:	FT-CAP, Temperature Stable, Automotive Grade
RoHS:	Yes
Termination:	Flexible Termination
Marking:	No
Failure Rate:	N/A
Approvals:	AEC-Q200
AEC-Q200:	Yes

Specifications	
Capacitance:	4700 pF
Capacitance Tolerance:	10%
Voltage DC:	100 VDC, 16000 V ESD Level
ESD Level per AEC-Q200:	16,000 V ESD Level
Dielectric Withstanding Voltage:	250 V
Temperature Range:	-55/+125C
Temperature Coefficient:	COG
Dissipation Factor:	0.1%
Aging Rate:	0% Loss/Decade Hour
Insulation Resistance:	100 GOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.