


Surface Mount Resistor Kit

0805 Case Size



RoHS
Compliant

Specifications Table


Type	Power Rating	Resistance Tolerance	Nominal Resistance
MC 0805	0.1W (1/10W)	±5%	10Ω

Ratings:

Type	MC 0805
Power Rating	0.1W (1/10W)
Rated Current(Jumper)	2A
Max. Overload Current(Jumper)	5A
Max. Working Voltage	150V
Max. Overload Voltage	300V
Dielectric Withstanding Voltage	500V
Temperature Range	-55°C +155°C
Ambient Temperature	+70°C

Power Rating:

Resistors shall have a power rating based on continuous load operation at an ambient temperature of 70°C . For temperature in excess of 70°C , The load shall be derate as shown in figure.



Surface Mount Resistor Kit


0805 Case Size




Nominal Resistance:

Effective figures of nominal resistance shall be in accordance with E-24 and E-96 series
E-96 series for 1% and E-24 series for 2% and 5%

Construction:



Power Rating and Dimensions:



Dimension :

Type	Dimension (mm)				
	$L \pm 0.15$	$W +0.15 / -0.1$	$H \pm 0.1$	$l1 \pm 0.2$	$l2 \pm 0.2$
MC 0805	2	1.25	0.55	0.4	0.4

Power Rating :

Type	Power Rating	Tolerance	Resistance	Standard Series
MC 0805	0.1W (1/10W)	Jumper	< 50mΩ	E-12
		±5	10Ω ~ 1MΩ	



Surface Mount Resistor Kit

0805 Case Size



Performance Specification :

Characteristics	Limits	Test Methods (JIS C 5201-1)
Insulation resistance	1,000 MΩ or more	Apply 500V DC between protective coating and termination for 1 min, then measure
Dielectric withstanding voltage	No evidence of flashover mechanical damage, arcing or insulation break down	Apply 300V AC between protective coating and termination for 1 minute
Temperature coefficient	1Ω - 10Ω : ±400 PPM/°C 11Ω - 100Ω : ±200 PPM/°C >100Ω : ±100 PPM/°C	Natural resistance change per temp. degree centigrade. $\frac{R_2 - R_1}{R_1(t_2 - t_1)} \times 10^6 \text{ (PPM/°C)}$ R ₁ : Resistance value at room temperature (t ₁) R ₂ : Resistance value at room temp. plus 100°C (t ₂)
Short time overload	Resistance change rate is ± (2.0% + 0.1Ω) Max.	Permanent resistance change after the application of a potential of 2.5 times RCWV for 5 seconds
Solderability	95 % coverage Min.	Test temperature of solder : 245 ± 3°C Dwell time in solder : 2 ~ 3 seconds
Soldering temp. Reference	Electrical characteristics shall be satisfied. Without distinct deformation in appearance. (95 % coverage Min.)	<p><u>Wave soldering condition:</u> (2 cycles Max.) Pre-heat : 100°C to 120°C, 30 ±5 sec. Suggestion solder temp.: 235°C to 255°C, 10 sec. (Max.) Peak temp.: 260°C</p> <p><u>Reflow soldering condition:</u> (2 cycles Max.) Pre-heat : 150°C to 180°C, 90 to 120 sec. Suggestion solder temp.: 235°C to 255°C, 20 to 40 sec. Peak temp.: 260°C</p> <p><u>Hand soldering condition:</u> The soldering iron tip temperature should be less than 300°C and maximum contract time should be 5 sec.</p>



Surface Mount Resistor Kit


0805 Case Size



Characteristics	Limits	Test Methods (JIS C 5201-1)															
Soldering Heat	Resistance change rate is: $\pm(1\% +0.05\Omega)$ Max.	Dip the resistor into a solder bath having a temperature of $260^{\circ}\text{C} \pm 3^{\circ}\text{C}$ and hold it for 10 ± 1 seconds.															
Temperature cycling	Resistance change rate is $\pm(1\% +0.05\Omega)$ Max.	Resistance change after continuous 5 cycles for duty cycle specified below :															
		<table border="1"> <thead> <tr> <th>Step</th> <th>Temperature</th> <th>Time</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>$-55^{\circ}\text{C} \pm 3^{\circ}\text{C}$</td> <td>30 mins</td> </tr> <tr> <td>2</td> <td>Room temp.</td> <td>10 to 15 mins</td> </tr> <tr> <td>3</td> <td>$+155^{\circ}\text{C} \pm 2^{\circ}\text{C}$</td> <td>30 mins</td> </tr> <tr> <td>4</td> <td>Room temp.</td> <td>10 to 15 mins</td> </tr> </tbody> </table>	Step	Temperature	Time	1	$-55^{\circ}\text{C} \pm 3^{\circ}\text{C}$	30 mins	2	Room temp.	10 to 15 mins	3	$+155^{\circ}\text{C} \pm 2^{\circ}\text{C}$	30 mins	4	Room temp.	10 to 15 mins
		Step	Temperature	Time													
		1	$-55^{\circ}\text{C} \pm 3^{\circ}\text{C}$	30 mins													
		2	Room temp.	10 to 15 mins													
3	$+155^{\circ}\text{C} \pm 2^{\circ}\text{C}$	30 mins															
4	Room temp.	10 to 15 mins															
Load life in humidity	Resistance change rate is $\pm(3\% +0.1\Omega)$ Max.	Resistance change after 1,000 hours (1.5 hours "on", 0.5 hour "off") at RCWV in a humidity chamber controlled at $40^{\circ}\text{C} \pm 2^{\circ}\text{C}$ and 90 to 95 % relative humidity															
Load Life	Resistance change rate is $\pm(3\% +0.1\Omega)$ Max.	Permanent resistance change after 1,000 hours operating at RCWV, with duty cycle of (1.5 hours"on", 0.5 hour "off") at $70^{\circ}\text{C} \pm 2^{\circ}\text{C}$ ambient															
Terminal bending	Resistance change rate is $\pm(1\% +0.05\Omega)$ Max.	Twist of Test Board : Y/X = 5/90mm for 10 seconds															

Kit resistors:

Insert for Chip Kit



Dimensions : Millimetres

www.element14.com
www.farnell.com
www.newark.com




Surface Mount Resistor Kit

0805 Case Size



Album for Chip Kit:



Dimensions : Millimetres

Chip Kit Resistors:

Product : MC Kit (0805) +/-5%
 E12 Series : 62 values (0R&10R to 1M)
 Quantity : 100pcs per value
 Total Qty : 6,200pcs.

NO.	Value
1	0E
2	10R
3	12R
4	15R
5	18R
6	22R
7	27R
8	33R
9	39R
10	47R

NO.	Value
11	56R
12	68R
13	82R
14	100R
15	120R
16	150R
17	180R
18	220R
19	270R
20	330R

NO.	Value
21	390R
22	470R
23	560R
24	680R
25	820R
26	1K
27	1K2
28	1K5
29	1K8
30	2K2

NO.	Value
31	2K7
32	3K3
33	3K9
34	4K7
35	5K6
36	6K8
37	8K2
38	10K
39	12K
40	15K



Surface Mount Resistor Kit

0805 Case Size



NO.	Value
41	18K
42	22K
43	27K
44	33K
45	39K
46	47K
47	56K
48	68K
49	82K
50	100K

NO.	Value
51	120K
52	150K
53	180K
54	220K
55	270K
56	330K
57	390K
58	470K
59	560K
60	680K

NO.	Value
61	820K
62	1M

Part Number Table

Description	Part Number
Resistor Kit, 0805, E-12, 5%	MC0805WAJE012KIT

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell Limited 2016.

