

This document was generated on 05/23/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0431603103

Status: **Active**

Sabre™ Power Connector Overview:

Sabre™ Right Angle Header, 3 Circuits, Glow Wire Capable, PCB Thickness 1.60mm, **Description:**

with Board Lock

Documents:

Packaging Specification PK-43789-001 (PDF) 3D Model RoHS Certificate of Compliance (PDF) Drawing (PDF)

Product Specification PS-44441-9999-001 (PDF) Product Literature (PDF)

Agency Certification

CSA LR19980 UL E29179

General

PCB Headers Product Family Series 43160

Application Power, Wire-to-Board

Comments

"Fully Polarized, high power wire to board and wire to wire connector system<P><P>This Molex product is manufactured from material that has the following ratings, tested by independent agencies:. a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13.. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12.and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety, section 30 Resistance to heat and fire. <P><P> The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-use standard(s). <P> If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for

possible product options."

Sabre™ Power Connector

Product Literature Order No 987650-5662 **Product Name** Sabre™ **UPC** 800754378215

Physical

Overview

Breakaway No Circuits (Loaded) 3 Circuits (maximum) 3 Color - Resin Black Durability (mating cycles max) 25 First Mate / Last Break No Flammability 94V-0 Glow-Wire Compliant Yes Guide to Mating Part No **Keying to Mating Part** Yes Lock to Mating Part Yes Material - Metal **Brass**



Series image - Reference only

EU ELV

Not Relevant

EU RoHS China RoHS

Compliant

REACH SVHC

Not Contained Per -ED/01/2017 (12 January 2017)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com Please visit the Contact Us section for any non-product compliance questions.

China ROHS Green Image **ELV** Not Relevant **RoHS Phthalates** Not Contained

Search Parts in this Series

43160 Series

Mates With

44441-2003 Sabre™ Receptacle Housing

Material - Plating Mating Tin Material - Plating Termination Tin

Material - Resin High Temperature Thermoplastic

Net Weight 4.495/g Number of Rows 1

Orientation Right Angle 3.81mm PC Tail Length **PCB** Locator Yes **PCB** Retention Yes PCB Thickness - Recommended 1.60mm Packaging Type Tray Pitch - Mating Interface 7.50mm Pitch - Termination Interface 7.50mm Plating min - Mating 0.889µm Plating min - Termination 0.889µm Polarized to Mating Part Yes Polarized to PCB Yes Shrouded Fully Stackable No Surface Mount Compatible (SMC) No

Temperature Range - Operating -40°C to +75°C Termination Interface: Style Through Hole

Electrical

Current - Maximum per Contact 18.0A Voltage - Maximum 600V

Solder Process Data

Duration at Max. Process Temperature (seconds)

Lead-freeProcess Capability

Max. Cycles at Max. Process Temperature

O01

Process Temperature max. C

235

Material Info

Reference - Drawing Numbers

Packaging Specification PK-43789-001
Product Specification PS-44441-9999-001

This document was generated on 05/23/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION