

Aluminum Electrolytic, 85C, ALC10, 270 uF, 20%, 550 V, -40/+85C



Dimensions	
D	35mm +1mm
L	50mm +/-2mm
S	10mm +/-0.1mm
LL	6.3mm +/-1mm
F	2mm +/-0.1mm

Packaging Specifications	
Sleeving:	Yes
Packaging:	Bulk

General Information	
Dielectric:	Aluminum Electrolytic
Series:	ALC10
Description:	Snap-In, Aluminum Electrolytic
RoHS:	Yes
Lead:	2 Pin
Notes:	Dimensions D And L Include Sleeving

Specifications	
Capacitance:	270 uF
Capacitance Tolerance:	20%
Voltage DC:	550 VDC, 605 VDC (Surge)
Temperature Range:	-40/+85C
Rated Temperature:	85C
Life:	15000 Hrs (Rated Voltage And Ripple Current At 85C), 24000 Hrs (Rated Voltage At 85C)
Resistance:	1290 mOhms (100Hz 20C), 1126 mOhms (10kHz 20C)
Current:	2.01 Amps (100Hz 85C), 3.15 Amps (10kHz 85C)
Leakage Current:	891 uAmps (5min 20C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.