


Aluminum Electrolytic, 85C, ALC10, 1000 uF, 20%, 400 V, -40/+85C



**Dimensions**

<b>D</b>	40mm +1mm
<b>L</b>	80mm +/-2mm
<b>S</b>	22.5mm +/-0.1mm
<b>LL</b>	6.3mm +/-1mm
<b>F</b>	2mm +/-0.1mm

**Packaging Specifications**

<b>Weight:</b>	131 g
<b>Sleeving:</b>	Yes
<b>Packaging:</b>	Bulk
<b>Packaging Quantity:</b>	25

**General Information**

<b>Dielectric:</b>	Aluminum Electrolytic
<b>Series:</b>	ALC10
<b>Description:</b>	Snap-In, Aluminum Electrolytic
<b>RoHS:</b>	Yes
<b>Lead:</b>	4 Pin
<b>Notes:</b>	Dimensions D And L Include Sleeving

**Specifications**

<b>Capacitance:</b>	1000 uF
<b>Capacitance Tolerance:</b>	20%
<b>Voltage DC:</b>	400 VDC, 440 VDC (Surge)
<b>Temperature Range:</b>	-40/+85C
<b>Rated Temperature:</b>	85C
<b>Life:</b>	18000 Hrs (Rated Voltage And Ripple Current At 85C), 29000 Hrs (Rated Voltage At 85C)
<b>Resistance:</b>	120 mOhms (100Hz 20C), 78 mOhms (10kHz 20C)
<b>Current:</b>	5 Amps (100Hz 85C), 8.82 Amps (10kHz 85C)
<b>Leakage Current:</b>	2400 uAmps (5min 20C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.