


Aluminum Electrolytic, 85C, ALC10, 0.01 F, 20%, 63 V, -40/+85C



Dimensions	
D	40mm +1mm
L	35mm +/-2mm
S	22.5mm +/-0.1mm
LL	6.3mm +/-1mm
F	2mm +/-0.1mm

Packaging Specifications	
Weight:	57 g
Sleeving:	Yes
Packaging:	Bulk

General Information	
Dielectric:	Aluminum Electrolytic
Series:	ALC10
Description:	Snap-In, Aluminum Electrolytic
RoHS:	Yes
Lead:	4 Pin
Notes:	Dimensions D And L Include Sleeving

Specifications	
Capacitance:	0.01 F
Capacitance Tolerance:	20%
Voltage DC:	63 VDC, 72.45 VDC (Surge)
Temperature Range:	-40/+85C
Rated Temperature:	85C
Life:	18000 Hrs (Rated Voltage And Ripple Current At 85C), 29000 Hrs (Rated Voltage At 85C)
Resistance:	80 mOhms (100Hz 20C), 72 mOhms (10kHz 20C)
Current:	4.58 Amps (100Hz 85C), 4.67 Amps (10kHz 85C)
Leakage Current:	3780 uAmps (5min 20C)