

Relay Module - PR2-RSC3-LDP-24DC/4X21AU - 2834724

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Preassembled relay modules with screw connection, consisting of: Relay socket, industrial relay with integrated LED, free-wheeling diode and engage/disengage manual actuate lever, and retaining bracket. Input voltage: 24 V DC, four PDTs with gold-plated contacts, 5 A


The figure shows the 24 V DC version

Why buy this product

- With DC types, freewheeling diode is integrated in relay
- Relay with detectable manual operation and status LED
- Mechanical switch position indicator
- 4 PDT types with multi-layer gold contacts
- Logical contact arrangement thanks to 1/3-level relay base



Key Commercial Data

Packing unit	5 STK
Minimum order quantity	5 STK
GTIN	 4 046356 044554
GTIN	4046356044554
Weight per Piece (excluding packing)	115.270 g
Custom tariff number	85364900
Country of origin	Japan

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

Width	27 mm
Height	78.5 mm
Depth	86 mm

Relay Module - PR2-RSC3-LDP-24DC/4X21AU - 2834724

Technical data

Ambient conditions

Ambient temperature (operation)	-25 °C ... 60 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C

Coil side

Nominal input voltage U_N	24 V DC
Input voltage range in reference to U_N	see diagram
Typical input current at U_N	38 mA
Typical response time	13 ms
Typical release time	14 ms
Protective circuit	Damping diode
Operating voltage display	Green LED
Power dissipation for nominal condition	0.91 W

Contact side

Contact type	4 PDTs
Type of switch contact	Single contact
Contact material	AgNi, hard gold-plated
Maximum switching voltage	250 V AC/DC
Minimum switching voltage	1 V
Min. switching current	1 mA
Maximum inrush current	12 A (15 ms)
Limiting continuous current	5 A
Interrupting rating (ohmic load) max.	1250 VA (for 250 V AC)
	120 W (at 24 V DC)
	110 W (at 48 V DC)
	78 W (at 60 V DC)
	55 W (at 110 V DC)
	77 W (at 220 V DC)

General

Test voltage relay winding/relay contact	2 kV (50 Hz, 1 min.)
Test voltage relay contact/relay contact	2 kV (50 Hz, 1 min.)
Operating mode	100% operating factor
Degree of protection	RT I (Relay)
Mechanical service life	5×10^7 cycles
Mounting position	any
Assembly instructions	In rows with zero spacing

Connection data input side

Connection name	Coil side
Connection method	Screw connection
Stripping length	7 mm
Conductor cross section solid	0.14 mm ² ... 2.5 mm ²

Relay Module - PR2-RSC3-LDP-24DC/4X21AU - 2834724

Technical data

Connection data input side

Conductor cross section flexible	0.14 mm ² ... 2.5 mm ²
Conductor cross section AWG	26 ... 14

Connection data output side

Connection name	Contact side
Connection method	Screw connection
Stripping length	7 mm
Conductor cross section solid	0.14 mm ² ... 2.5 mm ²
Conductor cross section flexible	0.14 mm ² ... 2.5 mm ²
Conductor cross section AWG	26 ... 14

Standards and Regulations


Standards/regulations	IEC 60664
	EN 50178
	IEC 62103
Degree of pollution	2
Overvoltage category	II

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"


Drawings

Circuit diagram



DC coils


Diagram




Operating voltage range of relay $T_u = T_{coil}$

Relay Module - PR2-RSC3-LDP-24DC/4X21AU - 2834724

Diagram




Diagram



AC interrupting rating

DC interrupting rating

Diagram



Electrical service life

Articles in set

Relay socket - PR2-BSC3/4X21 - 2833576



Relay socket PR2-B, for industrial relay REL-IR with 2 or 4 PDT, 1/3-level version, screw connections, connection facility for input/interference suppression modules, for mounting on NS 35/7.5

Single relay - REL-IR/LDP- 24DC/4X21AU - 2834096



Pluggable industrial relays with power contacts and additional hard gold plating, 4 PDT, test button, status LED, free-wheeling diode, mechanical switch position indicator, polarity A1+, A2-, coil voltage: 24 V DC

Relay Module - PR2-RSC3-LDP-24DC/4X21AU - 2834724

Articles in set

Retaining bracket - EL2-P35 - 2833592



Relay retaining bracket, with eject function and integrated equipment marking area (8 x 25 mm), to suit relay socket PR2, for 35 mm high industrial relay

Classifications

eCl@ss

eCl@ss 5.0	27371601
eCl@ss 5.1	27371601
eCl@ss 6.0	27371601
eCl@ss 7.0	27371601
eCl@ss 8.0	27371601
eCl@ss 9.0	27371601

ETIM

ETIM 2.0	EC001437
ETIM 3.0	EC001437
ETIM 4.0	EC001437
ETIM 5.0	EC001437
ETIM 6.0	EC001437

UNSPSC

UNSPSC 6.01	30211916
UNSPSC 7.0901	39121515
UNSPSC 11	39121515
UNSPSC 12.01	39121515
UNSPSC 13.2	39122334

Approvals

Approvals

Approvals


EAC / EAC


Ex Approvals

Approval details

Relay Module - PR2-RSC3-LDP-24DC/4X21AU - 2834724

Approvals

EAC		7500651.22.01.00244
-----	---	---------------------

EAC		EAC-Zulassung
-----	---	---------------