

## Marker for terminal blocks - UCT-TM 6 - 0828736

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: THERMOMARK CARD, BLUEMARK CLED, BLUEMARK LED, TOPMARK LASER, THERMOMARK PRIME, Mounting type: Snap into tall marker groove, for terminal block width: 6.2 mm, Lettering field: 5.6 x 10.5 mm

### Why buy this product

- The multi-section marking strips are easy to fit and can be easily separated if required
- Labeling service: Phoenix Contact can custom-label all UniCard markers according to your requirements
- The markers, which are supplied in uniform sheets, can be labeled quickly, easily, and precisely using the THERMOMARK CARD and the BLUEMARK LED
- The sheets provide space for including function texts
- The UCT-TM... UniCard labeling range includes markers for products with tall marker grooves

### Key Commercial Data

|                                      |   |
|--------------------------------------|---|
| Packing unit                         | 10 STK  |
| Minimum order quantity               | 10 STK  |
| GTIN                                 | <br>4 046356 522465 |
| GTIN                                 | 4046356522465   |
| Weight per Piece (excluding packing) | 14.120 g  |
| Custom tariff number                 | 39269097  |
| Country of origin                    | Poland  |

### Technical data

#### Dimensions

|            |         |
|------------|---------|
| Length (b) | 10.5 mm |
| Width (a)  | 5.6 mm  |
| Height     | 4.76 mm |

#### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 120 °C |
|---------------------------------|-------------------|

#### General

# Marker for terminal blocks - UCT-TM 6 - 0828736

## Technical data

### General

|   |                                     |
|---|-------------------------------------|
| Note  | Can be labeled via thermal transfer |
| Color   | white                               |
| Components  | free from silicone and halogen      |
| Flammability rating according to UL 94                              | V0                                  |
| Material  | PC                                  |
| Wipe resistance   | DIN EN 61010-1 (VDE 0411-1)         |
| Number of individual labels   | 60                                  |
| Number of individual labels per row                                 | 10                                  |
| RoHS compliant  | Yes                                 |
| Printability  | Thermal transfer                    |
|   | Inkjet printing                     |
| Device  | 5146464 THERMOMARK CARD             |
|   | 5146480 THERMOMARK CARD-UCT-MAG1    |
|   | 5147888 BLUEMARK LED                |
|   | 5147999 BLUEMARK CLED               |
| Ink ribbon  | 0801371 THERMOMARK-RIBBON 110-TC    |
|   | 5147421 BLUEMARK FLUID-CARTRIDGE    |
|   | 5146662 BLUEMARK CLED-FLUID-CARTR.  |
| Test for substances that would hinder coating with paint or varnish | VW PV 3.10.7:2005-02                |
| Result  | Test passed                         |
| Test specification weathering-resistance                            | Following ISO 4892-2:2013-03        |
| Test duration   | 96 h                                |
| Wipe resistance test result   | Test passed                         |
| Salt spray test specification                                       | DIN EN ISO 9227:2012-09             |
| Test duration   | 96 h                                |
| Salt spray testing result   | Test passed                         |
| Alternating condensation climate with SO2 test specification        | DIN 50018:2013-05                   |
| Climate level   | AHT 1.0 S                           |
| Cycles  | 2                                   |
| Condensation test result  | Test passed                         |
| Wipe resistance of test specification inscriptions                  | IEC 61010-1:2010-06                 |
| Result  | Test passed                         |
| Marking mounting type   | Snap into tall marker groove        |

### Standards and Regulations

|  |                             |
|--|-----------------------------|
| Wipe resistance                        | DIN EN 61010-1 (VDE 0411-1) |
| Flammability rating according to UL 94 | V0                          |

## Drawings

# Marker for terminal blocks - UCT-TM 6 - 0828736

Pictogram



## Classifications

eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 24190208 |
| eCl@ss 4.1 | 24190208 |
| eCl@ss 5.0 | 27149103 |
| eCl@ss 5.1 | 27141137 |
| eCl@ss 6.0 | 27141137 |
| eCl@ss 7.0 | 27141137 |
| eCl@ss 8.0 | 27141137 |
| eCl@ss 9.0 | 27141137 |

ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC000761 |
| ETIM 6.0 | EC000761 |

UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121410 |
| UNSPSC 12.01  | 39121410 |
| UNSPSC 13.2   | 39131505 |

## Accessories

Accessories

Magazine

Magazine - THERMOMARK CARD-UCT-MAG1 - 5146480



Magazine for the THERMOMARK CARD printer, for accommodating UCT sheets (UCT-TM..., UCT1-TM..., UCT5-TM...)

## Marker for terminal blocks - UCT-TM 6 - 0828736

### Accessories

Magazine - TMP-UCT-MAG1 - 0803342



Magazine for the THERMOMARK PRIME printer, for accommodating UCT-TM..., UCT1(U)-TM..., UCT5-TM..., UCT-EM (5x10), UCT-EM (6x10)

---

Phoenix Contact 2016 © - all rights reserved  
<http://www.phoenixcontact.com>