

KEMET Part Number: C1812V334KCRACTU
(C1812V334KCRAC7800)

Ceramic, Anti-Arcing, ArcShield-(CxxxxV), 0.33 uF, 10%, 500 V, 1812, X7R, SMD, MLCC, ArcShield, High Voltage, Temperature Stable



Dimensions

L	4.5mm +/-0.3mm
W	3.2mm +/-0.3mm
T	2.1mm +/-0.20mm
B	0.6mm +/-0.35mm

Packaging Specifications

Packaging:	T&R, 180mm, Plastic Tape
Packaging Quantity:	500

General Information

Style:	SMD Chip
Series:	ArcShield-(CxxxxV)
Chip Size:	1812
Description:	SMD, MLCC, ArcShield, High Voltage, Temperature Stable
Features:	High Voltage, Temperature Stable
RoHS:	Yes
Termination:	Tin
Marking:	No
Failure Rate:	N/A
Miscellaneous:	Note: Referee time for X7R dielectric for this part number is 1000 hours. X7R dielectric is not recommended for AC line filtering or pulse applications

Specifications

Capacitance:	0.33 uF
Capacitance Tolerance:	10%
Voltage DC:	500 VDC
Dielectric Withstanding Voltage:	750 V
Temperature Range:	-55/+125C
Temperature Coefficient:	X7R
Dissipation Factor:	2.5%
Aging Rate:	3% Loss/Decade Hour
Insulation Resistance:	303 MOhms