

Dual Switching Diode




Features:

- Low current leakage
- Fast switching speed and low cost
- Small outline surface mount package
- Epoxy meets UL 94 V-0 flammability rating
- Moisture sensitivity level 1

**RoHS
Compliant**

Connection Diagram



SOT-23

Maximum Ratings and Electrical Characteristics

Rating at 25°C Ambient Temperature Unless Otherwise Specified.

Characteristic	Symbol	Rating	Units
Reverse Voltage	V_R	75	V
Forward Continuous Current	I_F	250	mA
Power Dissipation	P_{TOT}	350	mW
Peak Forward Surge Current @ $t = 1s$, Non-Repetitive	I_{FSM}	1	A
Maximum Instantaneous Forward Voltage $I_{FM} = 10mA$; $T_J = 25^\circ C$ (Notes 1)	V_F	855	mV
Maximum DC Reverse Current $V_R = 75V$ @ $T_J = 25^\circ C$ at Rated DC Blocking Voltage @ $T_J = 150^\circ C$	I_R	2.5 50	μA
Typical Junction Capacitance Measured at 1.0MHz, $V_R = 0V$	C_J	2	pF
Max. Thermal Resistance Junction To Ambient	$R_{\theta JA}$	357	k/W
Reverse Recovery Time $I_F = 10mA$ $V_R = 0V$ $R_L = 500\Omega$	T_{rr}	4	nS
Operating Temperature Range	T_J	-55 to +150	$^\circ C$
Storage Temperature Range	T_{STG}	-55 to +150	$^\circ C$

- Notes: 1. Pulse test: Pulse width 300 μ sec, Duty cycle 2%.
2. The typical data above is for reference only

Rating and Characteristic Curves

Fig. 1 Forward Characteristics






Fig. 2 Leakage Current vs Junction Temperature



Dual Switching Diode



Dimension:



SOT-23		
Dim.	Min.	Max.
A	2.8	3.04
B	2.1	2.64
C	1.2	1.4
D	0.89	1.03
E	1.78	2.05
F	0.45	0.6
G	0.013	0.1
H	0.89	1.12
J	0.085	0.18
K	0.37	0.51

Dimensions : Millimetres

Part Number Table

Description	Part Number
Dual Switching Diode	BAW56+

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell Limited 2016.

