

Surface Mount Rectifier



RoHS
Compliant

Features:

- Plastic package has UL Flammability Classification 94V-0
- Construction utilizes void-free molded plastic technique
- For surface mounted applications
- High temperature : 250°C/10 seconds at terminals.



Mechanical Data:

Case	: JEDEC Mini MELF(DO-213AA) molded plastic body
Terminals	: Solder plated,solderable per MIL-STD-750,method 2026
Polarity	: Colour band denotes cathode end
Mounting Position	: Any
Weight	: 0.0005 ounce, 0.015 gram
Reverse Voltage	: 50 to 1000 Volts
Forward Current	: 1 Ampere

Maximum Ratings and Electrical Characteristics:

Rating at 25°C ambient temperature unless otherwise specified.

Single phase, half wave, 60Hz, resistive or inductive load.

For capacitive load, derate current by 20%.

Characteristics	Symbol	LL4001G+	LL4002G+	LL4004G+	LL4007G+	Unit
Max. Recurrent Peak Reverse Voltage	V_{RRM}	50	100	400	1000	V
Max. RMS Voltage	V_{RMS}	35	70	280	700	
Max. DC Blocking Voltage	V_{DC}	50	100	400	1000	
Max. Average Forward Rectified Current 0.375" (9.5mm) lead length at $T_A = 75^\circ\text{C}$	$I_{(AV)}$	1				A
Peak Forward Surge Current 8.3ms Single Half Sine-Wave $T_A = 75^\circ\text{C}$	I_{FSM}	25				
Max. Instantaneous Forward Voltage at 1A	V_F	1.1				V
Max. DC Reverse Current at at Rated DC Blocking Voltage at $T_A = 25^\circ\text{C}$ $T_A = 125^\circ\text{C}$	I_R	5 100				μA
Typical Junction Capacitance (Note 1)	C_J	15				pF
Typical Thermal Resistance (Note 2) (Note 3)	$R_{\theta JA}$ $R_{\theta JL}$	75 30				$^\circ\text{C/W}$
Operating Temperature Range	T_J	-65 to +175				$^\circ\text{C}$
Storage Temperature Range	T_{STG}	-65 to +175				$^\circ\text{C}$

Notes:

1. Measured at 1.0MHz and applied reverse voltage of 4.0 Volts
2. Thermal resistance from junction to ambient, 0.24×0.24" (6.0×6.0mm) copper pads to each terminal
3. Thermal resistance from junction to terminal, 0.24×0.24" (6.0×6.0mm) copper pads to each terminal
4. The typical data above is for reference only

Surface Mount Rectifier



Ratings and Characteristic Curves

FIG.1 – Forward Current Derating




FIG.2 – Typical Instantaneous Forward characteristics




FIG.3 – Maximum Non-Repetitive Peak forward Surge Current




FIG.4 – Typical Reverse Characteristics






FIG.5 – Typical Junction



Surface Mount Rectifier



MiniMELF (Do-213AA)



Dimensions : Inches (Millimetres)

Part Number Table

Description	Part Number
Surface Mount Rectifiers	LL4001G+
	LL4002G+
	LL4004G+
	LL4007G+

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell Limited 2016.

