

KEMET Part Number: C1808C150KHGACTU
(C1808C150KHGAC7800)

Ceramic, Commercial-(CxxxxC), 15 pF, 10%, 3,000 V, 1808, COG, SMD, MLCC, Ultra-Stable, Low Loss, Class I



General Information

Style:	SMD Chip
Series:	Commercial-(CxxxxC)
Chip Size:	1808
Description:	SMD, MLCC, Ultra-Stable, Low Loss, Class I
Features:	Ultra-Stable, Low Loss, Class I
RoHS:	Yes
Termination:	Tin
Marking:	No
Failure Rate:	N/A

Dimensions

L	4.7mm +/-0.5mm
W	2mm +/-0.2mm
T	1.6mm +/-0.15mm
B	0.6mm +/-0.35mm

Packaging Specifications

Packaging:	T&R, 180mm, Plastic Tape
Packaging Quantity:	1000

Specifications

Capacitance:	15 pF
Capacitance Tolerance:	10%
Voltage DC:	3000 VDC
Dielectric Withstanding Voltage:	3,600 V
Temperature Range:	-55/+125C
Temperature Coefficient:	COG
Dissipation Factor:	0.1%
Aging Rate:	0% Loss/Decade Hour
Insulation Resistance:	100 GOhms