


Film, Metallized Polypropylene, DC Link, C4AE, 27 uF, 5%, 1,100 V, 70C, Lead Spacing = 52.5mm



General Information	
Dielectric:	Metallized Polypropylene
Style:	Radial
Series:	C4AE
RoHS:	Yes
Termination:	Tin
Lead:	4 Wire Leads
Miscellaneous:	Thermal Resistance = 10 C/W

Dimensions	
L	57.5mm +0.8mm
H	50mm +0.3mm
T	35mm +0.5mm
S	52.5mm +/-0.4mm
S1	20.3mm +/-0.4mm
LL	6mm -2mm
F	1.2mm NOM
G	0.5mm NOM

Specifications	
Capacitance:	27 uF
Capacitance Tolerance:	5%
Voltage DC:	1100 VDC
Temperature Range:	-40/+85C
Rated Temperature:	70C
Max dVdt:	13 V
Resistance:	4.9 mOhms (10kHz 70C)
Current:	16.5 Amps (10kHz 70C), 354 Amps (Peak)
Inductance:	35 nH

Packaging Specifications	
Packaging:	Bulk, Box