

Aluminum Electrolytic, 85C, ALS60, 1800 uF, 20%, 550 V, -40/+85C



General Information	
<b>Dielectric:</b>	Aluminum Electrolytic
<b>Series:</b>	ALS60
<b>Description:</b>	High Voltage, Screw Terminal, Aluminum Electrolytic
<b>Features:</b>	High Voltage
<b>RoHS:</b>	Yes
<b>Notes:</b>	Dimensions D And L Include Slewing. MS (MxH) = M12x16

Dimensions	
<b>D</b>	77mm +/-1mm
<b>L</b>	105mm +/-2mm
<b>T</b>	5.5mm +/-0.5mm
<b>S</b>	31.8mm +/-0.5mm
<b>DT</b>	13mm +/-0.5mm
<b>LT</b>	110.5mm +/-1mm
<b>TD</b>	10mm MIN
<b>V</b>	19mm NOM
<b>Z</b>	10mm NOM

Specifications	
<b>Capacitance:</b>	1800 uF
<b>Capacitance Tolerance:</b>	20%
<b>Voltage DC:</b>	550 VDC, 605 VDC (Surge)
<b>Temperature Range:</b>	-40/+85C
<b>Rated Temperature:</b>	85C
<b>Life:</b>	20000 Hrs
<b>Resistance:</b>	166.5 mOhms (100Hz 20C), 147 mOhms (10kHz 20C)
<b>Current:</b>	10.33 Amps (100Hz 85C), 15.99 Amps (10kHz 85C)
<b>Leakage Current:</b>	5940 uAmps (5min 20C)

Packaging Specifications	
<b>Weight:</b>	690 g
<b>Slewing:</b>	Yes
<b>Packaging:</b>	Bulk

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.