


Aluminum Electrolytic, 85C, ALS70, 0.027 F, 20%, 250 V, -40/+85C



Dimensions	
D	77mm +/-1mm
L	220mm +/-2mm
T	5.5mm +/-0.5mm
S	31.8mm +/-0.5mm
DT	13mm +/-0.5mm
LT	224.5mm +/-1mm
TD	10mm MIN
V	19mm NOM
Z	10mm NOM

Packaging Specifications	
Weight:	1.45 kg
Slewing:	Yes
Packaging:	T&R

General Information	
Dielectric:	Aluminum Electrolytic
Series:	ALS70
Description:	Screw Terminal, Aluminum Electrolytic
RoHS:	Yes
Notes:	Dimensions D And L Include Slewing. MS (MxH) = M12x 16

Specifications	
Capacitance:	0.027 F
Capacitance Tolerance:	20%
Voltage DC:	250 VDC, 288 VDC (Surge), 400 VDC (Surge)
Temperature Range:	-40/+85C
Rated Temperature:	85C
Life:	20000 Hrs (Rated Voltage And Ripple Current At 85C), 40000 Hrs (Rated Voltage At 85C)
Resistance:	15 mOhms (100Hz 20C), 12 mOhms (10kHz 20C)
Current:	25.1 Amps (100Hz 85C), 30.5 Amps (10 kHz 85C)
Leakage Current:	6000 uA