

Film, Double Metallized Polypropylene, Commercial Grade, R76, 0.01 uF, 5%, 630 V, 85C, Lead Spacing = 7.5mm



General Information	
Dielectric:	Double Metallized Polypropylene
Style:	Radial
Series:	R76
Features:	Pulse
RoHS:	Yes
Lead:	Cut
Approvals:	AEC-Q200
AEC-Q200:	Yes
Miscellaneous:	Voltage Derating: 1.35%/C Above 75C (AC), 1.25%/C Above 85C (DC)

Dimensions	
L	10.5mm +0.2mm
H	12mm +0.1mm
T	6mm +0.1mm
S	7.5mm +/-0.4mm
LL	4mm +1.5mm
F	0.6mm +/-0.05mm

Specifications	
Capacitance:	0.01 uF
Capacitance Tolerance:	5%
Voltage DC:	630 VDC
Voltage AC:	250 VAC
Temperature Range:	-55/+105C
Rated Temperature:	85C
Dissipation Factor:	0.1% 1kHz, 0.06% 10kHz, 0.1% 100kHz
Insulation Resistance:	100 GOhms
Max dVdt:	2,800 V
Inductance:	8 nH

Packaging Specifications	
Packaging:	Bulk
Packaging Quantity:	1000